

# Indestructible HI POWER LED HEADLIGHT

HEADLIGHT

**RAYOVAC**



LIFETIME WARRANTY

**300**  
LUMENS

**30**  
Foot (9m)  
DROP TESTED

VIRTUALLY  
**INDESTRUCTIBLE**

DIYHPHL3-BC

## ▪ 300 Lumen High Performance LED

- 60 lumens on energy saver
- 2 light modes: High & Energy Saver
- 150 meter beam distance on high
- 75 meter beam distance on energy saver

## ▪ Lifetime Warranty

- 30-Foot Drop Tested
- Water Resistant to IPX4
- Over-mold rubber pivoting head
- Shatterproof lens & reflector
- Impact resisting internal engineering

## • 3-Hour Runtime on high

- 14-Hour Runtime on energy saver

## • Head strap included: moisture-wicking cloth

## • Includes (3) AAA Alkaline Batteries



**RAYOVAC**

Skus #	DIYHPHL3-BC	Availability	October 2015
Description	Indestructible 3AAA High Power LED Headlight	Case UPC	10012800524614
Pkg UPC	012800524617	Case dimensions	13.000" X 5.125" X 7.000"
Pkg Dimensions	2.875" x 3.938" x 6.000"	Case cubic feet	0.270 cu. ft.
Pkg Weight	0.350 lbs.	Case weight	1.950 lbs.
Pkg Style	Peggable Card	Case Qty	4
Ti X Hi= (cases/pallet)	26 x 5 = 130		