

Indestructible HI POWER LED HEADLIGHT

HEADLIGHT

RAYOVAC



LIFETIME WARRANTY

300
LUMENS

30
Foot (9m)
DROP TESTED



VIRTUALLY
INDESTRUCTIBLE

DIYHPL3-BC

▪ 300 Lumen High Performance LED

- 60 lumens on energy saver
- 2 light modes: High & Energy Saver
- 150 meter beam distance on high
- 75 meter beam distance on energy saver

▪ Lifetime Warranty

- 30-Foot Drop Tested
- Water Resistant to IPX4
- Over-mold rubber pivoting head
- Shatterproof lens & reflector
- Impact resisting internal engineering

• 3-Hour Runtime on high

- 14-Hour Runtime on energy saver

• Head strap included: moisture-wicking cloth

• Includes (3) AAA Alkaline Batteries



| | | | |
|----------------------------|--|-----------------|---------------------------|
| Sk# | DIYHPL3-BC | Availability | October 2015 |
| Description | Indestructible 3AAA High Power LED Headlight | Case UPC | 10012800524614 |
| Pkg UPC | 012800524617 | Case dimensions | 13.000" X 5.125" X 7.000" |
| Pkg Dimensions | 2.875" x 3.938" x 6.000" | Case cubic feet | 0.270 cu. ft. |
| Pkg Weight | 0.350 lbs. | Case weight | 1.950 lbs. |
| Pkg Style | Peggable Card | Case Qty | 4 |
| Ti X Hi= (cases/pallet) | 26 x 5 = 130 | | |