



DCBL720B
**20V MAX* LITHIUM ION XR
 BRUSHLESS HANDHELD
 BLOWER (BARE)**



The 20V MAX* Brushless Handheld Blower provides the ability to clear debris with an air volume of up to 400 cubic feet per minute at 90 miles per hour. With an ergonomic and extremely lightweight design (7.1 lbs. with 20V MAX* 5.0Ah battery--DCB205), the blower is easy to control and minimizes stress on the arm. The variable speed trigger and speed lock give the user full power control.

FEATURES & SPECS
WARRANTY
USER REVIEWS

FEATURES & SPECS

FEATURES

- Up to 400 CFM of air volume at 90 MPH to clear debris
- Innovative axial fan design that maximizes on air output and run time
- Low noise during operation - 61 dB(A). Ideal for noise sensitive regions and properties
- Part of the 20V MAX* system of tools
- High-efficiency brushless motor maximizing run time and motor life
- Lightweight and ergonomic design maximizes control and minimizes stress on your arm
- Variable trigger and speed lock for full power control

SPECIFICATIONS

AIR SPEED	90 MPH	AIR VOLUME (CUBIC FEET PER MINUTE)	400 CFM
BATTERIES INCLUDED	NO	NOISE RATING	61 DB(A)
POWER SOURCE	LITHIUM ION	PRODUCT TYPE	HANDHELD BLOWER
SYSTEM	20V MAX*	WEIGHT WITHOUT BATTERIES	5.9 LBS