



DCBL770X1

FLEXVOLT™ 60V MAX* HANDHELD BLOWER

★★★★★ (0)

The DEWALT 60V MAX* Handheld Blower powers through debris at 129 MPH. It features a variable speed trigger and speed lock for total power control, and its lightweight and ergonomic design maximizes control and minimizes stress on your arms. It has a 60V MAX* FLEXVOLT battery that powers 60V MAX* tools or it can be backwards compatible to work

[READ MORE](#) ▾

[BUY NOW](#)

FEATURES & SPECS

FEATURES

- Powers through debris at up to 423 CFM of air volume at 129 MPH
- Flat concentrator nozzle increases air speeds to 175 MPH to power through stubborn debris
- High-efficiency brushless motor maximizes run time and motor life
- Variable speed trigger and speed lock for total power control

- Lightweight and ergonomic design maximizes control and minimizes stress on your arm
- Designed to withstand everyday heavy-duty usage

SPECIFICATIONS

AIR SPEED (FLAT CONCENTRATOR)	175 MPH
AIR SPEED (ROUND NOZZLE)	129 MPH
AIR VOLUME (FLAT CONCENTRATOR)	287 CFM
AIR VOLUME (ROUND NOZZLE)	423 CFM
AMP HOUR	3.0 AH
BATTERIES INCLUDED	1
NOISE RATING	67 DB(A)
POWER SOURCE	LITHIUM ION
PRODUCT TYPE	HANDHELD BLOWER
SYSTEM	60V MAX*
WEIGHT	9.8 LBS

INCLUDES

- (1) DCB770 Handheld Blower
- (1) Concentrator Attachment
- (1) 60V MAX* 3Ah Battery
- (1) Charger

EXPLORE PRODUCTS SIMILAR

SIMILAR

BATTERIES &
CHARGERS

★★★★★ (3)