



DCD991P2
**20V MAX* XR LITHIUM ION
 BRUSHLESS 3-SPEED
 DRILL/DRIVER KIT**

FEATURES & SPECS

FEATURES & SPECS

FEATURES

- 3-speed, all-metal high performance transmission optimizes tool-to-task for fast application speeds and improved run-time
- Heavy-duty 1/2" ratcheting nitro-carburized metal chuck with carbide inserts for superior bit gripping strength
- LED Spotlight Mode features 20 minute shutoff function allowing for extended work time in dark or confined spaces
- DEWALT-built high power, high efficiency brushless motor delivers up to 57% more run time over brushed
- 3-Mode LED provides lighting in dark or confined spaces up to 20X brighter than previous model

SPECIFICATIONS

AMP HOUR	5	BATTERY TYPE	LITHIUM ION
CHUCK SIZE	1/2"	CHUCK TYPE	METAL RATCHETING
KIT BOX	KIT BOX	MAX POWER	820 UWO
NO LOAD SPEED	0-450 / 0-1300 / 0-2000 RPM	# OF SPEED SETTINGS	3
POWER TOOL TYPE	CORDLESS	SYSTEM	20V MAX*
TOOL WEIGHT	4.6 LBS	UNITS WATTS OUT	820

INCLUDES

- DCD991 - 20V MAX* XR Lithium Ion Brushless Premium 3-Speed Drill/Driver
- (2) DCB205 - 20V MAX* XR High Capacity Li-Ion Batteries (5.0Ah)
- Charger
- Belt hook
- 360° side handle
- Kitbox