



DCE155D1
20V MAX* CORDLESS ACSR
CABLE CUTTING TOOL KIT

The 20V MAX* Cordless ACSR Cable Cutting Tool cuts cable without distorting it for easier connector installation to help utility electricians increase productivity. The guillotine style blade slices cleanly through 1590 ACSR, 750 MCM Cu, or 1000 MCM Al. The blade is easily replaceable in the field to maximize uptime.

FEATURES & SPECS

FEATURES & SPECS

FEATURES

- Cuts up to 1590 ACSR, 750 MCM Copper or 1000 MCM Aluminum
- Bright LED light helps to illuminate cutting area
- LED light with 20 second delay provides visibility in dimly lit spaces
- Guillotine cutter maintains cable profile for easy connector installation
- Field serviceable / replaceable blade

SPECIFICATIONS

CABLE CAPACITY	1590 ACSR / 750 MCM CU / 1000 MCM AL	POWER TOOL TYPE	CORDLESS
SYSTEM	20V MAX*	TOOL HEIGHT	7.5 IN
TOOL LENGTH	12.75 IN	TOOL WEIGHT	7.4 LBS

INCLUDES

- DCE155 Cable Cutter
- (1) DCB203 Battery
- Charger
- Hang Hook
- Shoulder Strap
- Kit Box