

DEWALT



20V
LITHIUM ION

HEATEDGEAR

DCHJ061C1

20V/12V MAX* LITHIUM ION BLACK HOODED HEATED JACKET KIT

Up to 7 Hours of runtime on low setting using the 20V MAX* compact 1.5 Ah battery. 3 core heating zones which include L&R chest and mid-back. LED controller with 3 temperature settings. Premium 20V MAX* batteries stored in an efficient battery pocket. USB power source with 2 USB power ports. Built in hood with adjustable drawstrings. Battery pockets

FEATURES & SPECS

FEATURES

- 20V MAX* and 12V MAX* Batteries can provide hours of core body warmth and continuous heat**
- Up to 7 hours of runtime on low setting using the 20V Max* compact 1.5Ah battery.

- Durable water and wind resistant cotton twill outer shell.
- 3 core heating zones; upper left & right chest and mid-back.
- LED controller offers 3 temperature settings (high, medium, low) with pre-heat function
- USB Power Source accepts DEWALT 20V MAX* and 12V MAX* batteries, includes battery fuel gauge, and 2 USB power ports for charging portable electronics.
- Battery pocket expands to accept 20V MAX* XR Li-Ion batteries which provide hours of core body warmth and continuous heat.
- Available in sizes S-3XL

SPECIFICATIONS

| | |
|-----------------------|----------------------------|
| BATTERY SYSTEM | 20V/12V MAX |
| COLOR | BLACK & GRAY |
| HEAT SETTINGS | HIGH, MEDIUM, PREHEAT, LOW |
| HEAT ZONES | 3 - L/R CHEST |
| HOOD | YES |
| POCKETS | 4 |
| SHELL MATERIAL | COTTON TWILL |
| SIZE | S-3XL |

INCLUDES

- DCB201 20V MAX* Li-Ion Battery (1.5Ah)
- DCB091 USB Power Source
- Fast Charger