

DEWALT



20V
LITHIUM ION

HEATEDGEAR

DCHJ062C1

20V/12V MAX* LITHIUM ION CAMO HEATED JACKET KIT

Up to 5.5 Hours of runtime on low setting using the 20V MAX* compact 1.5 Ah battery. Soft water and wind resistant polyester outer shell. 4 core heating zones which include L&R chest, mid-back and collar. LED controller with 3 temperature settings. Premium 20V MAX* batteries stored in an efficient battery pocket. USB power source with 2 USB power ports. Battery pockets expands to accept DEWALT XR 4.0 Ah battery packets. Includes: DCHJ062 Heated Jacket, DCB201 20V MAX* Lithium-Ion Battery (1.5 Ah), Charger and DCB091 USB Power Source.

FEATURES & SPECS

FEATURES

- DEWALT 20V MAX* and 12V MAX* Batteries can provide hours of core body warmth and continuous heat**

- Up to 7 hours of runtime on low setting using the 20V MAX* compact 1.5Ah battery.
- TRUE TIMBER™ HTC CAMO for universal and year-round use
- Soft, quiet and water/wind resistant outer shell.
- 4 Core heating zones; upper left and right chest, mid-back, and collar.
- LED controller offers 3 temperature settings (high, medium, low) with pre-heat function
- Removable hood provides additional protection from the elements.
- USB Power Source accepts DEWALT 20V MAX* and 12V MAX* batteries, includes battery fuel gauge, and 2 USB power ports for charging portable electronics.
- Battery pocket expands to accept 20V MAX* XR Li-Ion batteries which provide hours of core body warmth and continuous heat.
- Available sizes S-3XL

SPECIFICATIONS

| | |
|-----------------------|------------------------------------|
| BATTERY SYSTEM | 20V/12V MAX |
| COLOR | TRUE TIMBER™ DS1 |
| HEAT SETTINGS | HIGH, MEDIUM, PREHEAT, LOW |
| HEAT ZONES | 4 - L/R CHEST, MID-BACK, COLLAR |
| HOOD | REMOVABLE |
| POCKETS | 7 |
| SHELL MATERIAL | NOISE-LIMITING AND WATER RESISTANT |
| SIZE | S-3XL |

INCLUDES

- DCB201 20V MAX* Li-Ion Battery (1.5Ah)
- DCB091 USB Power Source
- Fast Charger