



20V
LITHIUM ION

DCK492L2 20V MAX* PREMIUM 4-TOOL COMBO KIT

The DCK492L2 20V MAX* Premium 4-Tool Combo Kit includes a hammerdrill with a 3-speed transmission, reciprocating saw with a 4-position, keyless blade clamp, impact driver with visibility, and a 20V MAX LED work light.

FEATURES & SPECS

FEATURES & SPECS

FEATURES

- DCD985 20V MAX* hammerdrill with patented 3-speed, all-metal transmission and 1/2" all metal ratcheting chuck delivers 535 units watts out of maximum performance, faster application speed, and superior bit retention
- DCF885 20V MAX* 1/4" impact driver features 3 LED lights with 20-second delay to provide visibility without shadows
- DCS380 20V MAX* reciprocating saw with 4-position keyless blade clamp allows for quick blade change without touching blade or reciprocating shaft
- DCL040 20V MAX* LED work light delivers 110 lumens of light output

SPECIFICATIONS

NUMBER OF TOOLS	4	POWER TOOL TYPE	CORDLESS
PRODUCT TYPE INCLUDED	IMPACT DRIVER, HAMMER DRILL, RECIPROCATING SAW, WORKLIGHT	SYSTEM	20V MAX*

THIS KIT INCLUDES

DCL040 ▶ DCD985B ▶ DCS380B ▶ DCF885B ▶ DCB200 ▶

INCLUDES

- DCD985 1/2" Hammerdrill
- DCS380 Reciprocating Saw
- DCF885 1/4" Impact Driver
- DCL040 LED Work Light
- (2) 20V MAX* Lithium Ion 3.0 Ah Battery Packs
- Fast Charger
- 360° Side Handle
- Belt Hook
- Contractor Bag

GUARANTEED TOUGH.®

FOLLOW US:



COPYRIGHT© 2016 DEWALT. The following are trademarks for one or more DEWALT power tools, accessories, anchors and concrete adhesives: The yellow and black color scheme; the "D"-shaped air intake grill; the array of pyramids on the handgrip; the kit box configuration; and the array of lozenge-shaped humps on the surface of the tool.



Privacy Policy | Terms of Use | Safety Notices and Recalls | Power Tools Institute | Travel Safety with Cordless Tools | DEWALT Patent Information