

NEW



DCS491B  
**20V MAX\* 18G SWIVEL HEAD  
SHEARS (TOOL ONLY)**

**FEATURES & SPECS****FEATURES & SPECS****FEATURES**

- 360 degree tool free swivel head which allows user to access tight quarters while maintaining comfort.
- Cordless shears allows user to take the tool to the workplace.
- Cuts 7/32" strip which continuously curls out of the cutting area providing consistent and accurate cuts.

**SPECIFICATIONS**

CAPACITY (MILD STEEL)	18 GA.	CAPACITY (STAINLESS STEEL)	20 GA.
MINIMUM CUTTING RADIUS	5.5 IN	SBDCLASSIFICATION/1.0/10075.VOLTAGE	20V MAX*
STROKES/MIN	0-2,300 SPM		

**INCLUDES**

- Tool only