

NEW



DCS494B
20V MAX* 14GA SWIVEL HEAD
DOUBLE CUT SHEARS

FEATURES & SPECS

FEATURES & SPECS

FEATURES

- 360 degree tool free swivel head which allows user to access tight quarters while maintaining comfort.
- LED work light illuminates surface.
- Cuts 7/32" strip which continuously curls out of the cutting area providing consistent and accurate cuts.
- Cordless shears allows user to take the tool to the workplace

SPECIFICATIONS

CAPACITY (MILD STEEL)	14 GA.	CAPACITY (STAINLESS STEEL)	16 GA.
MINIMUM CUTTING RADIUS	5" IN	STROKES/MIN	2,450 SPM
SYSTEM	20V MAX*	TOOL LENGTH	15.5" IN
TOOL WEIGHT	4.6 LBS		

INCLUDES

- DCS494 (Tool Only)
- Hex wrench