

NEW

**DCS496B
20V MAX* 18GA SWIVEL HEAD
OFFSET SHEARS (TOOL ONLY)****FEATURES & SPECS****FEATURES & SPECS****FEATURES**

- Tool-free 360 swivel head which allows user to access tight quarters while maintaining comfort
- Offset shear design can easily cut through 20ga spiral duct seams.
- Cordless shears allows user to take the tool to the workplace.
- Offset shear design can easily turn and cut circles.
- LED work light illuminates surface.

SPECIFICATIONS

CAPACITY IN STEEL	18 GA.
MINIMUM CUTTING RADIUS	1.0 IN
STROKES/MIN	0 - 2,450 SPM
TOOL LENGTH	15.5 IN

CAPACITY (MILD STEEL)	18 GA.
POWER TOOL TYPE	CORDLESS
SYSTEM	20V MAX*
TOOL WEIGHT	3.7 LBS

INCLUDES

- DCS496 (Tool Only)
- Hex Wrench