

NEW



DCST970X1
**FLEXVOLT™ 60V MAX*
 STRING TRIMMER**

★★★★★ (0) [WRITE A REVIEW](#) ▶

The DEWALT 60V MAX* String Trimmer is designed to power through tough overgrowth and withstand everyday heavy-duty usage. It features a high-efficiency brushless motor that maximizes runtime and motor life, and its lightweight and ergonomic design maximizes control and minimizes stress on your arms. It has a 60V MAX* FLEXVOLT battery that powers 60V MAX* tools or it can be backwards compatible to work with 20V MAX* tools.

FEATURES & SPECS

FEATURES & SPECS

FEATURES

- Gear drive design powers through tough overgrowth
- High-efficiency brushless motor maximizes run time and motor life
- 15" cutting swath with 0.080" line (also accepts 0.095")
- Variable speed trigger with Hi/Lo speed control for added power or extended run time
- Lightweight and ergonomic design maximizes control and minimizes stress on your arms
- Designed to withstand everyday heavy-duty usage

SPECIFICATIONS

AMP HOUR	3.0 AH	BATTERIES INCLUDED	1
CUTTING SWATH	15 IN	FEED TYPE	BUMP FEED
LINE DIAMETER	0.080/.095 IN	POWER SOURCE	LITHIUM ION
PRODUCT TYPE	STRING TRIMMER	RPM	0-5,600/ 0-6,600 RPM
SYSTEM	60V MAX*	WEIGHT	12 LBS

INCLUDES

- (1) DCST970 String Trimmer
- (1) 60V MAX* 3Ah Lithium Ion Battery
- (1) Charger
- (1) Auxiliary handle
- (1) 0.080" prewound in the spool