



DW1927B
27/64" PILOT POINT® DRILL BIT
- BULK

FEATURES & SPECS

FEATURES & SPECS

FEATURES

- Pilot Point® Tip starts on contact for clean, accurate holes and reduces lock-up on breakthrough
- Tapered web provides greater durability to reduce breaking
- Note: Sizes 1/16" to 11/64" are split point drill bits
- No-Spin Shank eliminates the frustration of bit spinning in the chuck
- Size markings are located above the shank to prevent wearing away
- Std Jobber Length Fractional Sizes

SPECIFICATIONS

DIAMETER	27/64 IN	QTY	6
-----------------	----------	------------	---

GUARANTEED TOUGH.®

COPYRIGHT© 2016 DEWALT. The following are trademarks for one or more DEWALT power tools, accessories, anchors and concrete adhesives: The yellow and black color scheme; the "D"-shaped air intake grill; the array of pyramids on the handgrip; the kit box configuration; and the array of lozenge-shaped humps on the surface of the tool.

