





# ProTac® 2AA Professional Tactical Light

FL 1 STANDARD	HIGH	LOW
	<b>120</b> LUMENS	<b>14</b> LUMENS
	<b>1h 45min</b>	<b>21h</b>
	<b>110m</b>	<b>32m</b>
	<b>3000 cd</b>	<b>250cd</b>



Case Material: 6000 Series machined aircraft aluminum with anodized finish.

Dimensions/Weight: Length: 5.97"; 15.16 cm Head Diameter: 0.90"; 2.29 cm Barrel Diameter: 0.65"; 1.65 cm 3.4 oz.; 96 grams with battery

Lens: Tempered glass lens, o-ring sealed

Light Source: C4® LED technology, impervious to shock with a 50,000 hour lifetime

On/Off: Multi-function, push-button tactical tailswitch. One handed operation of momentary, variable intensity or strobe mode

Battery: Two (2) AA alkaline batteries

Features: LED Solid State Power Regulation provides maximum light output throughout battery life  
 IPX7 rated design; waterproof to 1 meter for 30 minutes  
 Anti-roll facecap  
 Removable pocket clip  
 Serialized for positive identification

Approvals: Meets applicable European Community directives

Warranty: Streamlight's Limited Lifetime Warranty warrants this product to be free of defect, including the LED, for a lifetime of use. We will repair, replace or refund the purchase price, at our option, of any Streamlight product that does not work as a result of a manufacturing defect for as long as you own it. This limited lifetime warranty excludes abuse, batteries, switches, electronics and normal wear and tear. Switches and electronics have a two (2) year warranty with proof of purchase.

Made in China

\* With batteries (Included in purchase)



Item		UPC	Part #
ProTac 2AA with white LED	Black	080926-88033-7	88033
Nylon Holster - ProTac 2AA		080926-88038-2	88038

