

# PolyStinger DS® LED Rechargeable Flashlight

FE-1 STANDARD	HIGH	MEDIUM	LOW
	185 LUMENS	95 LUMENS	45 LUMENS
	2h	3h 45min	7h 15min
	310m	219m	155m
	24,000cd	12,000cd	6000cd

Strobe runs for 5.5 hours



There is a real need to cut costs wherever possible, yet we cannot afford to forget about environmental issues. Streamlight rechargeable LED flashlights make good economic environmental sense. Over time they cost significantly less to operate decreasing the amount of batteries used, relieving the problem of battery disposal.

With Streamlight LED rechargeable flashlights, your company will not only save on the cost of batteries. Since LEDs have a long life and won't burn out or won't break, they never need to be replaced. Your light will always be ready when you need it.

More powerful and more economical, Streamlight rechargeable LED lighting tools pack a lot more power with ultra-bright white beams and long illumination times. They are more dependable and more cost-efficient than a "D" cell flashlight.

**Case Material:** Super-tough, non-conductive nylon polymer with non-slip rubberized comfort grip. Unbreakable polycarbonate lens with scratch-resistant coating. Available in black.

**Dims/Weight:** Length: 8.64 in. (21.95 cm); Diameter: Major Diameter: 1.76 in. (4.47 cm); Body Diameter: 1.21 in. (3.07 cm); 11.9 oz (338 grams)\*

**Light Source:** C4® LED technology, impervious to shock with a 50,000 hour lifetime.

**On/Off:** Multi-function, easy access head mounted push-button switch designed for extremely long life; tested at 1 million actuations and multi-function push-button tactical tailswitch where both switches offer full feature control independent of each other

**Battery:** 3-Cell, 3.6-Volt NiCd sub-C battery is rechargeable up to 1000 times

**Charging:** Fits existing Stinger chargers. Steady charger fully recharges in 10 hours on 100V, 120V, 230V or 240VAC, or 12VDC. 2.5 hour fast charger or PiggyBack® charger models available.

- Features:**
- IPX4 Rated for water resistant operation
  - LED Charge-continuity indicator on charger base
  - Serialized for positive identification.
  - 3 meter impact resistance tested.
  - Compact, snap-in charger mounts in any position.

**Approvals\*\*:** Most models meet applicable European Community Directives

**Warranty:** Streamlight warrants this product to be free of defect for a lifetime of use. We will repair, replace or refund the purchase price, at our option, of any Streamlight product that does not work or that you manage to break for as long as you own it. Of course, this limited lifetime warranty excludes abuse, batteries and chargers. Rechargeable batteries and chargers have a one (1) year warranty with proof of purchase.

*\*With battery (included in purchase).*

*All performance claims to ANSI/NEMA FL1-2009 Standard*

Item #	Description	UPC	Item #	Description	UPC
<i>Steady Charge</i>			<i>Fast Charge</i>		
76825	PolyStinger DS LED 230V AC/DC 2 Holders - Black	080926-76825-3	76827	PolyStinger DS LED 230V AC/DC FC - 2 holders - Black	080926-76827-7
76813	PolyStinger DS LED 120V AC/DC 2 Holders - Black	080926-76813-0	76835	PolyStinger DS LED 120V AC/DC FC - 2 holders - Black	080926-76835-2
76818	PolyStinger DS LED 100V AC/DC 2 Holders - Black	080926-76818-5	76826	PolyStinger DS LED 230V AC FC - Black	080926-76826-0
76824	PolyStinger DS LED 230V AC - Black	080926-76824-6	76814	PolyStinger DS LED 120V AC FC - Black	080926-76814-7
76811	PolyStinger DS LED 120V AC - Black	080926-76811-6	76815	PolyStinger DS LED DC FC - Black	080926-76815-4
76817	PolyStinger DS LED 100V AC - Black	080926-76817-8	<i>Fast Charge PiggyBack</i>		
76812	PolyStinger DS LED DC - Black	080926-76812-3	76845	PolyStinger DS LED 240V AC/DC 1 FC PiggyBack - Black	080926-76845-1
<i>Steady Charge PiggyBack</i>			76816	PolyStinger DS LED 120V AC/DC 1 FC PiggyBack - Black	080926-76816-1
76832	PolyStinger DS LED 120V AC/DC PiggyBack - Black	080926-76832-1	76836	PolyStinger DS LED 120V AC FC PiggyBack - Black	080926-76836-9
76833	PolyStinger DS LED 120V AC PiggyBack - Black	080926-76833-8	76837	PolyStinger DS LED DC FC PiggyBack - Black	080926-76837-6
76834	PolyStinger DS LED DC PiggyBack - Black	080926-76834-5	76810	PolyStinger DS LED (WITHOUT CHARGER)- Black	080926-76810-9





Item	UPC	Part #
DC2 direct wire charge cord	080926-22050-8	22050
DC1 Charge Cord	080926-22051-5	22051
120V AC charge cord	080926-22311-0	22311
100V AC charge cord	080926-22666-1	22666
230V AC charge cord	080926-22664-7	22664
240V AC charge cord	080926-22241-0	22241
Charger Holder Stinger (10 Hour)**	080926-75100-2	75100
Charger Holder Fast Charge (2.5 hour)**	080926-75103-3	75103
5 Unit Bank Charger, 120V	080926-75400-3	75400
5 Unit Bank Fast Charger, 120V	080926-75401-6	75401
5 Unit Bank Charger, 230V	080926-75600-7	75600
5 Unit Bank Fast Charger, 230V	080926-75601-4	75601
5 Unit Bank Charger, 100V	080926-75700-4	75700
5 unit bank charger 100V	080926-75701-1	75701

Item	UPC	Part #
Battery Stick (NiCd Batteries)	080926-75175-0	75175
PiggyBack® Charger Holder - Steady Charger & Battery**	080926-75275-7	75275
PiggyBack® Charger Holder Fast Charge & Battery**	080926-75276-4	75276
Battery Stick (NiCd Batteries)	080926-75175-0	75175
Safety Wand Blue	080926-75932-9	75932
Safety Wand Red	080926-75933-6	75933
Safety Wand Yellow	080926-75934-3	75934
Safety Wand White	080926-75938-1	75938
Safety Wand Glow in the Dark	080926-75943-5	75943
Holster, (Deluxe Nylon)	080926-75909-1	75909
Ring Holder	080926-75906-0	75906
Holster (Nylon)	080926-76090-5	76090
Loop holster	080926-75928-8	75928

\*\*Does not include cord

