

Table of Clamp Bolt Lengths and Part Numbers

Clamps	Part # End	Part # Mid	Size	"T" Bolt in.	"T" Bolt PN
Portrait	K10224-131	K10180-001	31 mm	1.77	B20015-012
Portrait	K10224-133	K10180-001	33 mm	1.77	B20015-012
Portrait	K10224-140	K10180-001	40 mm	1.77	B20015-012
Portrait	K10224-142	K10180-001	42 mm	1.77	B20015-012
Portrait	K10224-144	K10180-001	44 mm	1.77	B20015-012
Portrait	K10224-146	K10180-001	46 mm	1.77	B20015-012
Portrait	K10224-150	K10180-001	50 mm	1.77	B20015-012

Clamps	Part # End	Part # Mid	Size	"T" Bolt in.	"T" Bolt PN
Landscape	K10183-131	K10182-001	31 mm	2.10	B20015-002
Landscape	K10183-133	K10182-001	33 mm	2.10	B20015-002
Landscape	K10183-140	K10182-001	40 mm	2.10	B20015-002
Landscape	K10183-142	K10182-001	42 mm	2.10	B20015-002
Landscape	K10183-144	K10182-001	44 mm	2.10	B20015-002
Landscape	K10183-146	K10182-001	46 mm	2.10	B20015-002
Landscape	K10183-150	K10182-001	50 mm	2.10	B20015-002

Collar Nut					B20025-001
------------	--	--	--	--	------------

This table shows the nominal T-Bolt lengths for various PV Panels commonly used in the industry.

See www.sunmodo.com for current warranty documents and information.

SunModo Corporation
 1905 E 5th St., Suite A
 Vancouver, WA 98661
 Ph: 360-844-0048