



Dependable Power for Any Application

Product Datasheet

Snap In Breakers - 480 Primary Volts - 120/240 Secondary Volts - 1Ø Panel Tran Zone Power Centers - Single Phase

Catalog #: PT061150025LS



PRODUCT FEATURES

- Meets or exceeds UL, CSA, NEMA, ANSI, and OSHA standards
- Snap-in Breakers
- UL Type 3R Enclosure
- Shielded for cleaner power
- Covered under Acme's 10 year limited warranty

BENEFITS

- Fully compliant with NEC 450-3
- Designed for indoor and outdoor applications
- Electrostatic shield for enhanced protection
- Primary and Secondary main circuit breakers provided

UL STANDARD

UL 1062

CSA STANDARD

C22.2 No 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

kVA:	25.00
Primary Voltage:	480
Secondary Voltage:	120/240
Frequency:	60 Hz
ANFC Taps:	-
BNFC Taps:	2
Taps % Steps:	5%
Max Temperature Rise:	115°C
UL Insulation Class:	180°C
Primary Breaker:	ED42B090L (90A)
Secondary Breaker:	Q2125 (125A)

PRODUCT MEASUREMENTS

Height (In./cm):	41.88 (106.4)
Width (In./cm):	17.88 (45.4)
Depth (In./cm):	13.5 (34.3)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall

PACKAGING

Ship Weight (Lbs/Kg):	330 (150)
-----------------------	-----------

COMPLIANCES

UL Standard:	UL 1062
UL Listed:	File E56936
CSA Standard:	C22.2 No 47
CSA Listed:	LR7357-39
Warranty:	Acme Electric Warranty Card
	www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

