

Sealed Beam Lamp Specifications

Lamp No.	Primary Application	Design Volts	Design Watts or Amps	Approx. Initial Maximum Beam C.P.	Approx. Total Spread to 10% Max. C.P. (Degrees)		Rated Average Lab Life (Hours)	Base	Filament Designation	Max. Overall Length	
					Horiz.	Vert.				mm	in.
RECTANGULAR 142mm x 200mm (5.6 in x 7.9 in)											
H6054	Halogen Auto Headlamp, Type 2B1 ^{(130) (50)}	HI	12.8	65W			150 ⁽⁶⁰⁾	3 Contact Lugs	C-6	138	5%
H6054H0*	Performance Series Type 2B1 Headlamp ^{(130) (50)}	LO	12.8	35W	SAE Specifications		320 ⁽⁶⁰⁾		C-6		
HP6054	Halogen Auto Headlamp, Type 2B1 ^{(130) (50) (142)}	HI	12.8	65W			150 ⁽⁶⁰⁾	3 Contact Lugs	C-8	138	5%
H5054	Halogen Truck Headlamp, Type 2B1 ^{(130) (50)}	LO	12.8	35W	SAE Specifications		700 ⁽⁶⁰⁾		C-6		
6052	Auto Headlamp, Type 2B1 ⁽⁶⁰⁾	HI	12.8	65W			320 ⁽⁶⁰⁾	3 Contact Lugs	C-6	138	5%
6053	Truck Headlamp, Type 2B1 ⁽⁶⁰⁾	LO	12.8	55W	SAE Specifications		150 ⁽⁶⁰⁾		C-6		
		LO	12.8	55W	SAE Specifications		640 ⁽⁶⁰⁾	3 Contact Lugs	C-6	138	5%
PAR36 BULB 114mm (4 1/2 in) DIAMETER											
4546	Hand Lantern	4.7	.5A	6300	3	3	100	Screw Terminals	C-2R	70	2%
4546-1	Hand Lantern	4.7	.5A	6300	3	3	100	Slip-on Terminals	C-2R	70	2%
4547	Hand Lantern	4.75	1.25A	20,000	3	3	100	Screw Terminals	C-2R	70	2%
H7556	Halogen Emergency Bldg. Lighting ⁽¹³⁰⁾	6.0	6W	400	30	20	50	Screw Terminals	C-6	70	2%
7672-1	Emergency Bldg. Lighting	6.0	7.2W	350	30	20	50	Slip-on Terminals	C-6	70	2%
7613	Emergency Bldg. Lighting	6.0	8W	400	30	20	50	Screw Terminals	C-6	70	2%
7613-1	Emergency Bldg. Lighting	6.0	8W	400	30	20	50	Slip-on Terminals	C-6	70	2%
H7550	Halogen Hand Lantern ⁽¹³⁰⁾	6.0	8W	25,000	3	3	50	Screw Terminals	C-6	70	2%
H7550-1	Halogen Hand Lantern ⁽¹³⁰⁾	6.0	8W	25,000	3	3	50	Slip-on Terminals	C-6	70	2%
H7551	Halogen Emergency Bldg. Lighting ⁽¹³⁰⁾	6.0	8W	550	30	20	50	Screw Terminals	C-6	70	2%
H7552	Halogen Emergency Bldg. Lighting ⁽¹³⁰⁾	6.0	10W	650	30	20	50	Screw Terminals	C-6	70	2%
H7553	Halogen Emergency Bldg. Lighting ⁽¹³⁰⁾	6.0	12W	850	30	20	50	Screw Terminals	C-6	70	2%
H7554	Halogen Emergency Bldg. Lighting ⁽¹³⁰⁾	6.0	20W	1,400	30	20	50	Screw Terminals	C-6	70	2%
4614	Aircraft Navigation ⁽⁶⁰⁾	6.0	100W	85,000	11	6	300	Screw Terminals	C-6	70	2%
4511	Tractor	6.2	30W	2,300	Trapezoidal		300 ⁽⁶⁰⁾	Screw Terminals	C-6	70	2%
4516	Spotlamp	6.2	30W	45,000	9	4	300	Screw Terminals	C-6	70	2%
4042	Emergency Bldg. Lighting	6.4	12W	1,100	45	20	150	Screw Terminals	C-6	70	2%
4014	Emergency Bldg. Lighting	6.4	18W	1,500	50	25	200	Screw Terminals	C-6	70	2%
4308	Headlamp, Horse-Drawn Vehicles	6.4	25W	24,000	-	-	300		C-6		
4510	Tractor Flood, Emergency Bldg. Lighting	6.4	12W	3,000	-	-	150	3 Screw Terminals	C-6	70	2%
4515	Spotlamp ⁽⁶⁰⁾	6.4	25W	800	80	20	300	Screw Terminals	C-6	70	2%
H4515	Spotlamp, Shielded Bulb ⁽¹³⁰⁾	6.4	30W	55,000	5	5	100	Screw Terminals	C-6	70	2%
H7555	Halogen Emergency Bldg. Lighting ⁽¹³⁰⁾	6.4	30W	67,000	5 1/2	4	100	Screw Terminals	C-6	70	2%
4044	Emergency Bldg. Lighting	12.0	8W	550	30	20	50	Screw Terminals	C-6	70	2%
4044-1	Emergency Bldg. Lighting	12.0	12W	1,100	50	25	150	Screw Terminals	C-6	70	2%
H7557	Emergency Bldg. Lighting Halogen-Cycle ⁽¹³⁰⁾	12.0	12W	1,100	50	25	150	Slip-on Terminals	C-6	70	2%
4414	Warning Signal, Emergency Bldg. Lighting, Garden and Security Lighting	12.0	12W	850	30	20	50	Screw Terminals	C-6	70	2%
4414-1	Signal	12.8	18W	1,500	50	25	300	Screw Terminals	C-6	70	2%
4414A	Turn Signal, Warning Signal Yellow Lens	12.8	18W	1,500	50	25	300	Slip-on Terminals	C-6	70	2%
4414R	Turn Signal, Warning Signal Red Lens	12.8	18W	450	50	25	300	Screw Terminals	C-6	70	2%
7414Y	Signal, Light Yellow Lens	12.8	18W	275	50	25	300	Screw Terminals	C-6	70	2%
4446	Emergency Bldg. Lighting	12.8	18W	1,000	50	25	300	Screw Terminals	C-6	70	2%
4405	Spotlight ⁽⁶⁰⁾	12.8	25W	400	80	80	300	Screw Terminals	C-6	70	2%
H4405	Spotlamp, Shielded Bulb ⁽¹³⁰⁾	12.8	30W	50,000	6	5	100	Screw Terminals	C-6	70	2%
4416	Spotlamp, Signal	12.8	30W	66,000	7	4	100	Screw Terminals	C-6	70	2%
4416-1	Spotlamp, Signal	12.8	30W	35,000	11	4	300	Screw Terminals	C-6	70	2%
4416A	Signal, Light Yellow Lens Cover	12.8	30W	35,000	11	4	300	Slip-on Terminals	C-6	70	2%
4416R	Signal, Red Lens Cover	12.8	30W	26,000	11	4	300	Screw Terminals	C-6	70	2%
4406	Tractor, Flood ⁽¹³⁰⁾	12.8	30W	4,000	11	4	300	Screw Terminals	C-6	70	2%
4406-1	Tractor, Flood ⁽¹³⁰⁾	12.8	35W	600	80	30	300 ⁽⁶⁰⁾	Screw Terminals	C-6	70	2%
4409X	Farm Tractor ⁽¹²⁰⁾	12.8	35W	600	80	30	300 ⁽⁶⁰⁾	Slip-on Terminals	C-6	70	2%
4410	Backup Lamp, Tractor Flood	12.8	35W	600	80	30	300 ⁽⁶⁰⁾	Screw Terminals	C-6	70	2%
4411	Tractor	12.8	35W	600	80	30	300 ⁽⁶⁰⁾	Screw Terminals	C-6	70	2%
4411-1	Tractor	12.8	35W	3,000	Trapezoidal		300 ⁽⁶⁰⁾	Screw Terminals	C-6	70	2%
		12.8	35W	3,000	Trapezoidal		300 ⁽⁶⁰⁾	Slip-on Terminals	C-6	70	2%

THE PRODUCTS SHOWN REPRESENT ONLY A SMALL PORTION OF OUR STOCK
PLEASE CALL IF THE PRODUCT YOU NEED IS NOT LISTED
949/452-0900 • 800/8-LIGHTS • FAX: 800-255-3141