

Catalog Number: 10-305
Product ID: 7TAA008620R0022
UPC Number: 78378610305
Status: Active

Set Screw Wire Connector, Wire Range 18-12 AWG, Temperature Rating of 221 Degrees F (105 Degrees C), 600V, Orange

- The nylon insulating shells resist heat, cold and impact with a temperature rating of 105 degree C maximum.
- 600 Volt rated.
- Threaded brass inserts for vibration resistant connections.
- Easily removed with color-coded nylon insulating shells.

North American Specifications (UNSPSC)

UNSPSC	39121409 Wire connectors
IGCC	4543 Wire connectors
Brand Name	T&B
Type	Wire Connectors & Termination
Special Features	The nylon insulating shells resist heat, cold and impact with a temperature rating of 105 degree C maximum.
Standard	UL E9809, CSA 6591000
Wire Size	#18 - 12 AWG
Material	Nylon
Color	Orange
Voltage Rating	600V
Temperature Rating	105 Degrees Celsius (221 F)

Packaging

Inner Quantity	100
Inner Dimensions (inches)	5.3x3.3x2.3
Outer Quantity	1000
Outer Dimensions (inches)	16x7x6
Weight Uom	6.25 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com