



Dependable Power for Any Application

Product Datasheet

600Δ Primary Volts - 208Y/120 Secondary Volts - 3Ø Dry Type Distribution Transformer - Three Phase

Catalog #: T2A793321S



PRODUCT FEATURES

- UL listed, CSA certified
- Fully encapsulated core and coil
- Meet CSA C802.2 Efficiency
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

UL STANDARD

UL 506

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

| | |
|-----------------------|----------|
| kVA: | 9.00 |
| Primary Voltage: | 600Δ |
| Secondary Voltage: | 208Y/120 |
| Frequency: | 60 Hz |
| ANFC Taps: | - |
| BNFC Taps: | 2 |
| Taps % Steps: | 5.0% |
| Max Temperature Rise: | 115°C |
| UL Insulation Class: | 180°C |

PRODUCT MEASUREMENTS

| | |
|------------------|--------------|
| Height (In./cm): | 14.03 (36.0) |
| Width (In./cm): | 17.77 (45.1) |
| Depth (In./cm): | 11.52 (29.3) |

CONFIGURATION

| | |
|---------------------|---------------------|
| Construction Type: | Encapsulated |
| Mounting Type: | Wall |
| Knockouts (In./Cm): | 0.75-1.25 (1.9-3.2) |
| Wiring Diagram: | 28 |

PACKAGING

| | |
|-----------------------|------------|
| Ship Weight (Lbs/Kg): | 180 (81.6) |
|-----------------------|------------|

COMPLIANCES

| | |
|--|-----------------------------|
| UL Standard: | UL 506 |
| UL Listed: | File E79947 |
| CSA Standard: | C22.2 No. 47 |
| CSA Listed: | LR7357-32 |
| Warranty: | Acme Electric Warranty Card |
| www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf | |

