




Warranties and Certifications:	Item #	Description	Voltage	Wattage	Incandescent Wattage Comparison	Lumens	LPW	CCT	CRI	M.O.L. (inches)	Diameter (inches)	Case Quantity
 5 YEAR WARRANTY* For the most up-to-date specs, please visit www.tcpi.com <small>*Based on 12 hours use per day</small>	Smooth Uniform Dimming – Omni-Directional											
	10W A-Lamp											
	LED10A19D0D24K	Dimmable 10W Omni-Directional A19 - 2400K	120	10	60	800	80.0	2400K	82	4.5	2.6	12
	LED10A19D0D27K	Dimmable 10W Omni-Directional A19 - 2700K	120	10	60	800	80.0	2700K	82	4.5	2.6	12
	LED10A19D0D30K	Dimmable 10W Omni-Directional A19 - 3000K	120	10	60	825	82.5	3000K	82	4.5	2.6	12
	LED10A19D0D41K	Dimmable 10W Omni-Directional A19 - 4100K	120	10	60	850	85.0	4100K	82	4.5	2.6	12
	7W A-Lamp											
	LED7A19D0D24K	Dimmable 7W Omni-Directional A19 - 2400K	120	7	40	450	64.3	2400K	82	4.5	2.6	12
	LED7A19D0D27K	Dimmable 7W Omni-Directional A19 - 2700K	120	7	40	450	64.3	2700K	82	4.5	2.6	12
	LED7A19D0D30K	Dimmable 7W Omni-Directional A19 - 3000K	120	7	40	475	67.9	3000K	82	4.5	2.6	12
	LED7A19D0D41K	Dimmable 7W Omni-Directional A19 - 4100K	120	7	40	500	71.4	4100K	82	4.5	2.6	12
	Non-Dimmable Options – Omni-Directional											
	10W A-Lamp											
	LED10A19D0D27K	Non-Dimmable 10W Omni-Directional A19 - 2700K	120	10	60	800	80.0	2700K	82	4.3	2.4	12
	LED10A19D0D30K	Non-Dimmable 10W Omni-Directional A19 - 3000K	120	10	60	825	82.5	3000K	82	4.3	2.4	12
	7W A-Lamp											
	LED7A19D0D27K	Non-Dimmable 7W Omni-Directional A19 - 2700K	120	7	40	450	64.3	2700K	82	4.3	2.4	12
	LED7A19D0D30K	Non-Dimmable 7W Omni-Directional A19 - 3000K	120	7	40	475	67.9	3000K	82	4.3	2.4	12