



Elite A19 A-Lamps

Omni-Directional and All-Purpose

High efficiency A-Lamps. Light output in all directions to suit many applications.

Limitless options for the following applications:

- General Lighting
- Floor Lamps
- Ceiling Fixtures
- Table Lamps
- Sconces

Great features and benefits:

- Energy efficient: Up to 85% more efficient than incandescent alternatives
- Smooth, uniform dimming; also available as non-dimming
- Long life: Available in 25,000 hours or 15,000 hours
- Similar look and feel as incandescent alternative
- Excellent color consistency and high color rendering (CRI)
- Available in 2400K, 2700K, 3000K, 4100K and 5000K
- Fits any installations where a standard A19 bulb is used
- Rated for totally enclosed fixtures



All-Purpose A-Lamp



Omni-Directional A-Lamp



LED
we know light.™

TCP®

325 Campus Dr. | Aurora, Ohio 44202 | P: 800-324-1496 | tcp.com

©TCP MAY 2017 / WF49888 versionA






LED	Available in 25,000 Hours or 15,000 Hours average rated life, 120 Volts
------------	---

Applications:

Ideal for applications where uniform multi-directional light output is required.

- + Table Lamps
- + Floor Lamps
- + Sconces
- + Ceiling Fixtures
- + Decorative Fixtures

Features	Benefits
Up to 85% less energy than halogen alternatives	Instant energy savings
Long life	Minimizes replacement and maintenance costs
Very low heat generation	Perfect for sensitive display lighting such as art galleries
Excellent Color Consistency and CRI	Enhances colors of focal point while maintaining uniformity throughout lighting installation from lamp to lamp
UL approved for damp location	Can be used outdoors when protected from elements. Withstands humidity indoors/outdoors
Shatter resistant	Lower the risk of injury and breakage
ANSI construction compliant	Fits all A19 installations
Rated for totally enclosed fixtures	Can be used indoors or outdoors in enclosed fixtures



Specifications

Input Line Voltage:	120 VAC
Input Power	See Chart
Input Line Frequency	50/60HZ
Lamp Life (Rated)	25,000 hrs or 15,000 hrs
Minimum Starting Temp	-30°C
Maximum Operating Temp	40°C
CRI	80



- + Excellent "technical" A-Lamp replacement
- + Based on ENERGY STAR standard for omni-directional lamps
- + Supported by many utility rebates

- + Excellent "value" A-Lamp replacement
- + All-purpose lamp with excellent uniformity within 230 degrees that works well in all A-Lamp fixtures

5 YEAR WARRANTY* 25,000 HOUR LAMPS

3 YEAR WARRANTY* 15,000 HOUR LAMPS

*Based on 12 hours use per day

For the most up-to-date specs, please visit www.tcp.com





Warranties and Certifications	Item #	Description	Voltage	Wattage	Incandescent Wattage Comparison	Lumens	LPW	CCT	CRI	R9	M.O.L. (inches)	Diameter (inches)	Case Quantity
-------------------------------	--------	-------------	---------	---------	---------------------------------	--------	-----	-----	-----	----	-----------------	-------------------	---------------

LED ELITE (25,000 HOUR LAMP LIFE)

60W Equivalent Options



10W A19 Omni-Directional A-Lamp - DIMMABLE

LED10A19D0D24K	10W Omni Dimmable A-Lamp - 2400K	120	10	60	640	64.0	2400K	80	>0	4.3	2.4	12
LED10A19D0D27K	10W Omni Dimmable A-Lamp - 2700K	120	10	60	800	80.0	2700K	80	>0	4.3	2.4	12
LED10A19D0D30K	10W Omni Dimmable A-Lamp - 3000K	120	10	60	825	82.5	3000K	80	>0	4.3	2.4	12
LED10A19D0D41K	10W Omni Dimmable A-Lamp - 4100K	120	10	60	850	85.0	4100K	80	>0	4.3	2.4	12
LED10A19D0D50K	10W Omni Dimmable A-Lamp - 5000K	120	10	60	850	85.0	5000K	80	>0	4.3	2.4	12

10W A19 Omni-Directional A-Lamp - Non Dimmable

LED10A19D0D27K	10W Omni Non Dim A-Lamp - 2700K	120	10	60	800	80.0	2700K	80	>0	4.3	2.4	12
LED10A19D0D30K	10W Omni Non Dim A-Lamp - 3000K	120	10	60	825	82.5	3000K	80	>0	4.3	2.4	12
LED10A19D0D41K	10W Omni Non Dim A-Lamp - 4100K	120	10	60	850	85.0	4100K	80	>0	4.3	2.4	12

10W A19 All-Purpose A-Lamp - DIMMABLE

LED10A19D24K	10W Dimmable A-Lamp - 2400K	120	10	60	640	64.0	2400K	80	>0	4.3	2.4	12
LED10A19D27K	10W Dimmable A-Lamp - 2700K	120	10	60	800	80.0	2700K	80	>0	4.3	2.4	12
LED10A19D30K	10W Dimmable A-Lamp - 3000K	120	10	60	825	82.5	3000K	80	>0	4.3	2.4	12
LED10A19D41K	10W Dimmable A-Lamp - 4100K	120	10	60	850	85.0	4100K	80	>0	4.3	2.4	12
LED10A19D50K	10W Dimmable A-Lamp - 5000K	120	10	60	875	87.5	5000K	80	>0	4.3	2.4	12

40W Equivalent Options

7W A19 Omni-Directional A-Lamp - DIMMABLE

LED7A19D0D24K	7W Omni Dimmable A-Lamp - 2400K	120	7	40	450	64.3	2400K	80	>0	4.3	2.4	12
LED7A19D0D27K	7W Omni Dimmable A-Lamp - 2700K	120	7	40	450	64.3	2700K	80	>0	4.3	2.4	12
LED7A19D0D30K	7W Omni Dimmable A-Lamp - 3000K	120	6.8	40	560	82.4	3000K	80	>0	4.3	2.4	12
LED7A19D0D41K	7W Omni Dimmable A-Lamp - 4100K	120	6.5	40	520	80.0	4100K	80	>0	4.3	2.4	12
LED7A19D0D50K	7W Omni Dimmable A-Lamp - 5000K	120	6.8	40	545	80.1	5000K	80	>0	4.3	2.4	12

7W A19 All-Purpose A-Lamp - DIMMABLE

LED7A19D24K	7W Dimmable A-Lamp - 2400K	120	7	40	450	64.3	2400K	80	>0	4.3	2.4	12
LED7A19D27K	7W Dimmable A-Lamp - 2700K	120	7	40	425	60.7	2700K	80	>0	4.3	2.4	12
LED7A19D30K	7W Dimmable A-Lamp - 3000K	120	7	40	450	64.3	3000K	80	>0	4.3	2.4	12
LED7A19D41K	7W Dimmable A-Lamp - 4100K	120	7	40	500	71.4	4100K	80	>0	4.3	2.4	12
LED7A19D50K	7W Dimmable A-Lamp - 5000K	120	7	40	500	71.4	5000K	80	>0	4.3	2.4	12

LED (15,000 HOUR LAMP LIFE)

60W Equivalent Options



9W A19 All-Purpose A-Lamp - Non Dimmable

LED9A1927K	9W Non Dimmable A-Lamp - 2700K	120	9	60	800	88.9	2700K	80	>0	4.3	2.4	12
LED9A1930K	9W Non Dimmable A-Lamp - 3000K	120	9	60	825	91.7	3000K	80	>0	4.3	2.4	12
LED9A1941K	9W Non Dimmable A-Lamp - 4100K	120	9	60	850	94.4	4100K	80	>0	4.3	2.4	12
LED9A1950K	9W Non Dimmable A-Lamp - 5000K	120	9	60	850	94.4	5000K	80	>0	4.3	2.4	12

40W Equivalent Options

5W A19 All-Purpose A-Lamp - Non Dimmable

LED5A1927K	5W Non Dimmable A-Lamp - 2700K	120	5	40	450	90.0	2700K	80	>0	4.3	2.4	12
LED5A1930K	5W Non Dimmable A-Lamp - 3000K	120	5	40	475	95.0	3000K	80	>0	4.3	2.4	12
LED5A1941K	5W Non Dimmable A-Lamp - 4100K	120	5	40	500	100.0	4100K	80	>0	4.3	2.4	12
LED5A1950K	5W Non Dimmable A-Lamp - 5000K	120	5	40	525	105.0	5000K	80	>0	4.3	2.4	12

*Based on 12 hours use per day

For the most up-to-date specs, please visit www.tcp.com



CREATING BEAUTY

TCP has a **20-year history in energy-efficient lighting.**

Thanks to our **cutting edge technology** and manufacturing

expertise, we have shipped billions of high quality lamps and our

integrated technology and manufacturing

provides **expedited time-to-market.** With TCP, you can

count on unique lighting products designed to meet very specific needs—

lighting that transforms your surroundings and envelopes you in warmth—

lighting that generates beauty with every flip of the switch.

LED

For more information on the quality and care TCP can deliver, call us at **800.324.1496** or visit tcp.com

325 Campus Dr. | Aurora, Ohio 44202 | P: 800-324-1496 | F: 877-487-0516