



LED Dimmable Recessed Retrofits

TCP's Dimmable Retrofit Kits are the perfect choice for new construction, and retrofit opportunities when a sleek, integrated look is preferred.

Limitless options for the following applications:

- Dimmable 6", 5" & 4" downlight applications

Great features and benefits:

- 85W BR30/BR40, 65W BR30/BR40, and 50W R20 downlight replacement options
- Smooth, uniform dimming from 100% - 0.5%
- Highly efficient LEDs and Driver
- Long Life: 35,000 hours
- Consistent color within 3 MacAdam ellipse tolerance
- Easy installation—pigtail and spring clips



4" Dimmable Recessed Retrofit

5" & 6" Dimmable Recessed Retrofits



LED
we know light.™





LED Dimmable Recessed Retrofits Specifications

LED

35,000 Hours average rated life, 120Volts

Applications:

Ideal for dimmable 6", 5" & 4" downlight applications



Perfect for retrofit or new construction recessed downlight applications

Features and Benefits

- 5"/6" unit ideal for replacing dimmable 65W and 85W incandescent alternatives in 5" and 6" recessed cans
- 4" unit ideal for replacing 50W incandescent alternatives in a 4" recessed can
- Smooth, uniform dimming
- Highly efficient LEDs and Driver
- Long Life: 35,000 hours
- Consistent color within 3 MacAdam ellipse tolerance
- UL approved for damp locations
- Easy installation and integrated trim
- Shatter Resistant

Catalog Number

Notes

Type



Specifications


	14W	11W	10W
Recessed Downlight Size:	5", 6"	5", 6"	4"
Input Line Voltage:	120 VAC	120 VAC	120 VAC
Input Power	14 W	11 W	10 W
Input Line Frequency	50/60HZ	50/60HZ	50/60HZ
Lamp Life (Rated)	35,000 hrs	35,000 hrs	35,000 hrs
Minimum Starting Temp	-20°C	-20°C	-20°C
Maximum Operating Temp	40°C	40°C	40°C



- LED10DR427K
- LED10DR430K
- LED10DR435K
- LED10DR441K
- LED10DR450K



- LED11DR5627K
- LED11DR5630K
- LED11DR5641K
- LED11DR5650K
- LED14DR5627K
- LED14DR5630K
- LED14DR5641K
- LED14DR5650K

Warranties and Certifications:	Item #	Energy Star [®] RATED	Description	Life	Replacement	Voltage	Wattage	Lumens	LPW	CCT	CRI	Case Qty	
 5 YEAR WARRANTY <small>*Based on 12 hours usage per day</small>	Downlight Retrofits compatible with 5" & 6" recessed cans.												
	LED14DR5627K	★	LED 14W 5"/6" Recessed Downlight - 2700K	35,000	120	120	14	1250	89.3	2700K	82	6	
	LED14DR5630K	★	LED 14W 5"/6" Recessed Downlight - 3000K	35,000	120	120	14	1300	92.9	3000K	82	6	
	LED14DR5641K	★	LED 14W 5"/6" Recessed Downlight - 4100K	35,000	120	120	14	1300	92.9	4100K	82	6	
	LED14DR5650K	★	LED 14W 5"/6" Recessed Downlight - 5000K	35,000	120	120	14	1350	96.4	5000K	82	6	
	LED11DR5627K	★	LED 11W 5"/6" Recessed Downlight - 2700K	35,000	75	120	11	800	81.8	2700K	82	6	
	LED11DR5630K	★	LED 11W 5"/6" Recessed Downlight - 3000K	35,000	75	120	11	850	86.4	3000K	82	6	
	LED11DR5641K	★	LED 11W 5"/6" Recessed Downlight - 4100K	35,000	75	120	11	900	90.9	4100K	82	6	
	LED11DR5650K	★	LED 11W 5"/6" Recessed Downlight - 5000K	35,000	75	120	11	950	95.5	5000K	82	6	
	Downlight Retrofits compatible with 4" recessed cans.												
	LED10DR427K	★	LED 10W 4" Recessed Downlight - 2700K	35,000	75	120	10	750	75.0	2700K	82	6	
	LED10DR430K	★	LED 10W 4" Recessed Downlight - 3000K	35,000	75	120	10	750	75.0	3000K	82	6	
	LED10DR441K	★	LED 10W 4" Recessed Downlight - 4100K	35,000	75	120	10	800	80.0	4100K	82	6	
	LED10DR450K	★	LED 10W 4" Recessed Downlight - 5000K	35,000	75	120	10	800	80.0	5000K	82	6	

For the most up-to-date specs, please visit www.tcp.com