

TCP Elite Decorative lamps closely mimic the look and feel of incandescent but last much longer.

Limitless options for the following applications:

- Accent and decorative lighting
- Chandeliers
- Ceiling fans
- Indoor/outdoor fixtures

Great features and benefits:

- Energy efficient: 80% energy savings
- Replaces 25W and 40W incandescent lamps
- Smooth, uniform dimming—perfect for chandeliers
- Long life: 25,000 hours
- Excellent color consistency and high color rendering (CRI)
- UL damp location rated—excellent for use in outdoor applications



ELITE
SERIES by TCP



Candelabra G16 Globe*
Frosted and Clear

Candelabra Blunt Tip*
Frosted and Clear

Candelabra Flame Tip*
Clear

* Also available in an E26 base (frosted and clear)

LED
we know light.™



LED

25,000 hours average rated life, 120 volts

Applications

Ideal for decorative dimming applications. Suitable for outdoor fixtures. Also perfect for applications with hard to reach areas, vibration, and frequent starts.

Accent and decorative lighting including:

- + Chandeliers
- + Ceiling Fans
- + Decorative
- + Indoor Fixtures
- + Outdoor Fixtures
- + Wall Sconces



Light output equivalency:

5w = 40w
4w = 25w

Features and Benefits

- Long life: 25,000 hours—no more bulb replacements
- Fully dimmable, brilliant LED light
- Excellent white color consistency from bulb to bulb
- UL approved for dry and damp locations
- Available in E12 and E26 base

* Three or more lamps per dimming circuit is recommended for optimal dimming

Catalog Number


Notes

Type




Specifications (at full brightness)

Input Line Voltage:	120VAC
Input Line Frequency	60HZ
Lamp Life (Rated)	25,000 hrs
Minimum Starting Temp	-30°C
Maximum Operating Temp	40°C
UL/cUL Listed	Yes
Power Factor	92%
CRI	80



LED5E12G1627K
LED4E12G1627K



LED5E26G1627K
LED4E26G1627K



LED5E12B1127K
LED5E12B1130K
LED5E12B1150K
LED4E12B1124K
LED4E12B1127K




LED5E26B1127K
LED5E26B1130K
LED4E26B1124K
LED4E26B1127K




LED5E12F1127K
LED4E12F1127K



LED5E26F1127K
LED4E26F1127K



LED5E12G1627KF
LED4E12G1627KF



LED5E26G1627KF
LED4E26G1627KF



LED5E12B1127KF
LED5E12B1150KF
LED4E12B1127KF



LED5E26B1127KF
LED4E26B1127KF




LED5E26F1127KF
LED4E26F1127KF



3 YEAR WARRANTY

For the most up-to-date specs, please visit www.tcp.com



Warranties and Certifications:	Item #	Description	Voltage	Wattage	Wattage Equivalent	M.O.L. (inches)	Diameter (inches)	Lumens	LPW	CCT	CRI	
 3 YEAR WARRANTY	5W Decorative Lamps											
	LED5E12G1627K	LED 5W DIMMABLE CANDELABRA G16 GLOBE - 2700K	120	5.0	40W	3.5	2.0	350	70	2700K	80	
	LED5E26G1627K	LED 5W DIMMABLE G16 GLOBE - 2700K	120	5.0	40W	3.5	2.0	350	70	2700K	80	
	LED5E12G1627KF	LED 5W DIMMABLE CANDELABRA FROSTED G16 GLOBE - 2700K	120	5.0	40W	3.5	2.0	350	70	2700K	80	
	LED5E26G1627KF	LED 5W DIMMABLE FROSTED G16 GLOBE - 2700K	120	5.0	40W	3.5	2.0	350	70	2700K	80	
	LED5E12B1127K	LED 5W DIMMABLE CANDELABRA BLUNT TIP - 2700K	120	5.0	40W	3.8	1.4	350	70	2700K	80	
	LED5E12B1130K	LED 5W DIMMABLE CANDELABRA BLUNT TIP - 3000K	120	5.0	40W	3.8	1.4	375	75	3000K	80	
	LED5E12B1150K	LED 5W DIMMABLE CANDELABRA BLUNT TIP - 5000K	120	5.0	40W	3.8	1.4	400	80	5000K	80	
	LED5E26B1127K	LED 5W DIMMABLE BLUNT TIP - 2700K	120	5.0	40W	3.8	1.4	350	70	2700K	80	
	LED5E26B1130K	LED 5W DIMMABLE BLUNT TIP - 3000K	120	5.0	40W	3.8	1.4	375	75	3000K	80	
	LED5E12B1127KF	LED 5W DIMMABLE CANDELABRA FROSTED BLUNT TIP - 2700K	120	5.0	40W	3.8	1.4	350	70	2700K	80	
	LED5E12B1150KF	LED 5W DIMMABLE CANDELABRA FROSTED BLUNT TIP - 5000K	120	5.0	40W	3.8	1.4	400	80	5000K	80	
	LED5E26B1127KF	LED 5W DIMMABLE FROSTED BLUNT TIP - 2700K	120	5.0	40W	3.8	1.4	350	70	2700K	80	
	LED5E12F1127K	LED 5W DIMMABLE CANDELABRA FLAME TIP - 2700K	120	5.0	40W	3.8	1.4	350	70	2700K	80	
	LED5E26F1127K	LED 5W DIMMABLE FLAME TIP - 2700K	120	5.0	40W	3.8	1.4	350	70	2700K	80	
	LED5E26F1127KF	LED 5W DIMMABLE FROSTED FLAME TIP - 2700K	120	5.0	40W	3.8	1.4	350	70	2700K	80	
	4W Decorative Lamps											
	LED4E12G1627K	LED 4W DIMMABLE CANDELABRA G16 GLOBE - 2700K	120	4.0	25W	3.5	2.0	280	70	2700K	80	
	LED4E26G1627K	LED 4W DIMMABLE G16 GLOBE - 2700K	120	4.0	25W	3.5	2.0	280	70	2700K	80	
	LED4E12G1627KF	LED 4W DIMMABLE CANDELABRA FROSTED G16 GLOBE - 2700K	120	4.0	25W	3.5	2.0	280	70	2700K	80	
	LED4E26G1627KF	LED 4W DIMMABLE FROSTED G16 GLOBE - 2700K	120	4.0	25W	3.5	2.0	280	70	2700K	80	
	LED4E12B1124K	LED 4W DIMMABLE CANDELABRA BLUNT TIP - 2400K	120	4.0	25W	3.8	1.4	200	50	2400K	80	
	LED4E12B1127K	LED 4W DIMMABLE CANDELABRA BLUNT TIP - 2700K	120	4.0	25W	3.8	1.4	260	65	2700K	80	
	LED4E26B1124K	LED 4W DIMMABLE BLUNT TIP - 2400K	120	4.0	25W	3.8	1.4	200	50	2400K	80	
	LED4E26B1127K	LED 4W DIMMABLE BLUNT TIP - 2700K	120	4.0	25W	3.8	1.4	260	65	2700K	80	
	LED4E12B1127KF	LED 4W DIMMABLE CANDELABRA FROSTED BLUNT TIP - 2700K	120	4.0	25W	3.8	1.4	260	65	2700K	80	
	LED4E26B1127KF	LED 4W DIMMABLE FROSTED BLUNT TIP - 2700K	120	4.0	25W	3.8	1.4	260	65	2700K	80	
LED4E12F1127K	LED 4W DIMMABLE CANDELABRA FLAME TIP - 2700K	120	4.0	25W	3.8	1.4	260	65	2700K	80		
LED4E26F1127K	LED 4W DIMMABLE FLAME TIP - 2700K	120	4.0	25W	3.8	1.4	260	65	2700K	80		
LED4E26F1127KF	LED 4W DIMMABLE FROSTED FLAME TIP - 2700K	120	4.0	25W	3.8	1.4	260	65	2700K	80		

For the most up-to-date specs, please visit www.tcpi.com

CREATING BEAUTY

TCP has a **20-year history in energy-efficient lighting.**

Thanks to our **cutting edge technology** and manufacturing

expertise, we have shipped billions of high quality lamps. Our

integrated technology and manufacturing provides

expedited time-to-market. With TCP, you can count on

unique lighting products designed to meet very specific needs—lighting that

transforms your surroundings and envelopes you in warmth—**lighting**

that generates beauty with every flip of the switch.

LED

For more information on the quality and care TCP can deliver, call us at **800.324.1496** or visit tcp.com

325 Campus Dr. | Aurora, Ohio 44202 | P: 800.324.1496 | F: 877.487.0516