



Dependable Power for Any Application

Product Datasheet

Autotransformer - 600/480 Primary Volts - 480/380 Secondary Volts - 3Ø Dry Type Distribution Transformer - Three Phase

Catalog #: T2A527171



PRODUCT FEATURES

- UL listed, CSA certified
- Fully encapsulated core and coil
- UL Type 3R epoxy encapsulated
- Floor Mounted
- Ground Studs for use with non-metallic conduit
- Aluminum Bus termination
- Covered under Acme's 10 year limited warranty

BENEFITS

- Quiet operation with sound levels below NEMA standards

UL STANDARD

- UL 1561

CSA STANDARD

- C22.2 No. 47

WARRANTY

- Acme Electric Warranty Card
- www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

kVA:	300/240
Primary Voltage:	600/480
Secondary Voltage:	480/380
Frequency:	50/60 Hz
ANFC Taps:	-
BNFC Taps:	2
Taps % Steps:	5.0%
Max Temperature Rise:	150°C
UL Insulation Class:	220°C

PRODUCT MEASUREMENTS

Height (In./cm):	29.41 (74.7)
Width (In./cm):	28.15 (71.5)
Depth (In./cm):	22.37 (56.8)

CONFIGURATION

Construction Type:	Ventilated
Mounting Type:	Floor
Weather Shield:	WSA2
Wiring Diagram:	57

PACKAGING

Ship Weight (Lbs/Kg):	650 (294.8)
-----------------------	-------------

COMPLIANCES

UL Standard:	UL 1561
UL Listed:	File E12547
CSA Standard:	C22.2 No. 47
CSA Listed:	LR7357-32
Warranty:	Acme Electric Warranty Card
	www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

