



**GREENLEE.**  
A Textron Company

MADE FOR THE TRADE!™

ROPE-9/16 X 300' NYLON/POLYESTER

Double-Braided Composite Rope 9/16 x 300' (14.3 mm x 91 m)



Image  
Unavailable

Cat No: 35283

UPC No: 783310352839

### Description

---

- Double-braided inner core with an extra double-braided outer jacket for added strength and less stretch
- White with green tracer
- Rot and mildew resistant
- Factory spliced eyes at both ends
- Lowest stretch
- Select a rope with a maximum rated capacity that meets or exceeds the cable puller's maximum pulling force

### Specifications

---

- Application : For The UT4 And 640 Puller
- Average Breaking Strength : 16000.000 LB (71.100 KN)
- Color : White With Green Tracer
- Material : Nylon/Polyester
- Maximum Rated Capacity : 4000.000 LB (17.800 KN)
- Rope Diameter : 9/16 IN (14.300 MM)
- Rope Length : 300.000 FT (91.000 M)
- Rope Stand : 644
- Type : Double Braided
- Weight : 28.000 LB (12.700 KG)