



SEARCH  Sut

[Supplier Center](#) [Distributor Center](#)

**BROWSE PRODUCTS**

Category:  | Brand:

**PRODUCTS**

- [Bending](#)
- [Bolt Cutters](#)
- [Cable Termination](#)
- [CATV/Broadband Instruments](#)
- [Connectors](#)
- [Electric Test Instruments](#)
- [Fasteners](#)
- [Fiber Connections](#)
- [Fiber Optic Instruments](#)
- [Fishing](#)
- [Hydraulic Tools](#)
- [Knockouts](#)
- [Material Handling](#)
- [Power Tool Accessories](#)
- [Power Tools](#)
- [Professional Hand Tools](#)
- [Pulling](#)
- [Storage](#)
- [Telco Instruments](#)
- [VDV Instruments](#)
- [VDV Termination](#)
- [VDV Tools](#)
- [Wire Termination](#)

[Knockouts](#) > [KNOCKOUTS](#) > [Slug Buster](#) > PUNCH-RD 1.500 CONDUIT (721)

**PUNCH-RD 1.500 CONDUIT (721)**

[Images](#)



[SAVE PRODUCT TO PDF](#)

**Related Products**

 Image Unavailable



User Reviews  
[\(No Reviews Yet.\)](#)

Cat No: **721-1-1/2** UPC No: **783310317609**

[Where to Buy ▶](#)

- [Description](#)
- [Specifications](#)
- [Reviews](#)

- Application : For Slug-Buster Knockout Punches
- Capacity Mild Steel : 10 GA (3.500 MM)
- Size : 1.951 IN (49.600 MM)
- Sub Brand : Slug-Buster
- Type : Replacement, Round