



GREENLEE.
A Textron Company

MADE FOR THE TRADE!™

BENDER, HAND 1-1/4" EMT & 1" RIGID

Iron Hand Bender Head for 1-1/4" EMT, 1" Rigid & IMC



Image
Unavailable

Cat No: 843F

UPC No: 783310128342

Description

- Superior, patented Site-Rite sighting system featuring cast-in, readable markings on the bender heads and a finish that provides for the best visibility in low-light
- Choice of aluminum or iron alloy construction provides options depending on the user's preference for feel and weight
- Strong, stable square hook design
- 1-1/2" bender heads both offer the power pedal feature with a larger foot area on the head for greater control, stability and leverage
- 1/2", 3/4" & 1" bender heads all have enlarged foot pedals and increased toe room to ensure greater control, stability and leverage
- All the bender handles area consistent diameter, offering a bigger grip area, while still straight up and down for fast 30 degree bends
- Lifetime Limited Warranty

Specifications

- Centerline Bend Radius : 9-5/8" (244.500 MM)
- Conduit Type : EMT, IMC, Rigid
- Construction : Iron
- Marking : 10, 22-1/2, 30, 45, 60 & #176
- Pedal Type : Foot
- Sub Brand : SITE-RITE
- Type : Hand
- Weight : 16.200 LB (7.300 KG)