



**GREENLEE.**  
A Textron Company

MADE FOR THE TRADE!™

DMM, 600V AC/DC, 10A, CAP, TEMP (DM-45)

CATIII 600V Auto-Ranging Digital Multimeter



Image  
Unavailable

Cat No: DM-45

UPC No: 783310003373

### Description

---

- Large, easy-to-read displays
- Lifetime warranty
- Feature packed
- Replaceable fuses for easy field repair
- Frequency, capacitance, duty cycle, temperature, battery test and analog bar graph are just some of the features available on these meters

### Specifications

---

- Amperage Rating : 10
- Capacitance : 40, 400 nF; 4, 40, 200  $\mu$ F
- Counts : 4000
- Diode Test : Yes
- Display : Digital
- Field Replaceable Fuses : Yes
- Resistance : 400  $\Omega$ ; 4, 40, 400 k $\Omega$ ; 4, 40 M $\Omega$
- Standard : C/US ETL Listed, CATIII Approved
- Type : Auto/Manual Ranging
- Voltage Rating : 600