

TESTING & MEASUREMENT

BASIC ELECTRICAL KITS

Basic Electrical Kit



TK-30



DM-20

- Use to measure voltage and check 1.5 V and 9 V batteries.
- AC/DC voltage, DC amperage measurement.
- Built-in test leads, no loose parts to lose.
- Resistance measurement.
- Audible continuity and diode tests.
- Lifetime Limited Warranty.

SPECIFICATIONS

Amperage Measurement	DC A: 2000 μ A; 20.00, 200.00 mA
Voltage Measurement	AC V: 200.0, 300 V; DC V: 200.0, 2000 mV; 20.00, 200.0, 300 V
Resistance Measurement	200.0, 2000 Ω ; 20.00, 200.0, 2000 k Ω
Measurement Category	CAT II, 300V

TK-30IR



GT-11 AND GT-15

- Safe, non-contact voltage detection.
- Bright LED and audible alarm sound if voltage is present.
- On/Off switch for longer battery life.
- Convenient pen-size device easily fits into pockets or tool pouches.
- Lifetime Limited Warranty

GT-11

- Use to detect voltage in outlets, lighting fixtures, circuit breakers, wires and cables or to find a break in a wire.

SPECIFICATIONS

Voltage Detection	50 - 1000 VAC
Frequency	50-500 HZ
Measurement Category	CAT N, 1000X

GT-15

- Use to detect voltage in low voltage applications ranging from 12-90 volts AC.

SPECIFICATIONS

Voltage Detection	12 - 90 VAC
Frequency	50-500 HZ
Measurement Category	CAT II, 300V

TK-30GFI



GT-10 AND GT-10GFI

- Use to trouble shoot 120 V AC Grounded outlets
- Light sequence indicates correct or incorrect
- GT-10GFI also tests also tests GFI Receptacle
- Lifetime Limited Warranty

CAT. NO.	UPC NO.	DESCRIPTION
TK-30	12127	Electrical Kit, Basic
TK-30IR	89799	Electrical Kit, Low Voltage
TK-30GFI	10268	Electrical Kit, GFCI