



**GREENLEE.**  
A Textron Company

MADE FOR THE TRADE!™



#### SPEED PUNCH UNIT OILTIGHT 30MM

"Punch Unit (Oiltight Pushbutton w/Notches), 30.5 mm (1-7/32") Dia., SPEED PUNCH™ System"

Cat No: 52066505

UPC No: 783310022633

#### Description

---

- SPEED PUNCH™ saves time and money with every hole.
- Up to 3X's faster setup and disassembly. "No-Thread" punch design eliminates cross-threading.
- Available for Stainless Steel - 1/2" to 2" conduit size and Mild Steel - 1/2" to 4" conduit size, Metric ISO-16 to ISO-63, and 22mm & 30mm for Oil tight push buttons.

#### Specifications

---

- Application : For punching notched mounting holes (used with push buttons, selector switches, indicator lights and emergency stops) in mild steel, aluminum, fiberglass, and plastic.
- Capacity Mild Steel : Max: 12 gauge (2.5 mm).
- Diameter : Actual hole size: 30.5 mm (1-7/32")
- Draw Stud : Std. Draw Stud: 7212SP32 (3/8" X 4.00").
- Driver : Use with Greenlee Punch Drivers: LS50L - Battery-Powered Driver OR Hydraulic Drivers: 10383 - QUICK DRAW® FLEX, 34288 - QUICK DRAW® STANDARD, 33786 - QUICK DRAW 90®.
- Material : Carbon-Alloy Steel: Punch -Nickel Plated, Die - Black Oxide.
- Minimum Pilot Hole : 5/8" (15.9 mm)
- Operation : Must be used with other SPEEDPUNCH™ System components.
- Short Description : PUNCH UNIT (OIL TIGHT PUSH BUTTON W/NOTCHES), 30.5 MM (1-7/32") DIA., SPEED PUNCH™ SYSTEM
- Sub Brand : SPEED PUNCH™
- Type : Knockout Punches
- Weight : 2.65 lbs. (1.20 kg)