

Ty-Rap®

Catamount® Cable Ties

Catamount® Cable Fastening Systems

Catamount® Ties and Terminals fit the needs of general-purpose fastening and wire terminations. Installers quickly discover that Catamount products offer durable and value-priced cable bundling for a variety of commercial and residential construction applications. Electricians can also take advantage of other benefits in stocking Catamount products in their toolboxes, such as more terminals per bag in most popular sizes than leading comparable brands.

Catamount Ties and Terminals are offered in a wide range of sizes, styles and colors and meet listing requirements for most electrical termination and fastening projects. A choice of matching tools are also offered to provide quick and reliable installations.

Miniature — Series 18



CAT. NO.	LENGTH (IN.)	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-4-18-9-C	4.0	3/8"	Natural	100
L-4-18-0-C	4.0	3/8"	Black	100
L-6-18-9-C	6.4	1 1/8"	Natural	100
L-6-18-0-C	6.4	1 1/8"	Black	100
L-8-18-9-C	8.0	2"	Natural	100
L-8-18-0-C	8.0	2"	Black	100

Bulk packages available. Contact Customer Service.

Use QC-100, L-200, L-400-C or ERG-50 Installation Tools



Intermediate — Series 30



CAT. NO.	LENGTH (IN.)	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-5-30-9-C	5.6	1 1/4"	Natural	100
L-5-30-0-C	5.6	1 1/4"	Black	100
L-8-40-9-C	8.5	2"	Natural	100
L-8-40-0-C	8.5	2"	Black	100
L-11-40-9-C	11.5	3"	Natural	100
L-11-40-0-C	11.5	3"	Black	100
L-14-40-9-C	14.5	4"	Natural	100
L-14-40-0-C	14.5	4"	Black	100

Bulk packages available. Contact Customer Service.

Use QC-100, L-200, L-400-C or ERG-50 Installation Tools



Standard — Series 50



CAT. NO.	LENGTH (IN.)	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-5-50-9-C	5.5	1"	Natural	100
L-5-50-0-C	5.5	1"	Black	100
L-7-50-0-C	7.5	1 1/2"	Natural	100
L-7-50-9-C	7.5	1 1/2"	Black	100
L-11-50-9-C	11.1	3"	Natural	100
L-11-50-0-C	11.1	3"	Black	100
L-14-50-9-C	14.1	4"	Natural	100
L-14-50-0-C	14.1	4"	Black	100

Bulk packages available. Contact Customer Service.

Use QC-100, L-200, L-400-C or ERG-50 Installation Tools



Heavy-Duty — Series 120



CAT. NO.	LENGTH (IN.)	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-8-120-9-C	8.0	2"	Natural	100
L-8-120-0-C	8.0	2"	Black	100
L-11-120-9-C	11.1	3"	Natural	100
L-11-120-0-C	11.1	3"	Black	100
L-14-120-9-C	14.2	4"	Natural	100
L-14-120-0-C	14.2	4"	Black	100
L-18-120-9-L	18.0	4 3/8"	Natural	50
L-18-120-0-L	18.0	4 3/8"	Black	50
L-24-120-9-L	24.2	7"	Natural	50
L-24-120-0-L	24.2	7"	Black	50
L-28-120-9-L	28.0	8"	Natural	50
L-28-120-0-L	28.0	8"	Black	50

Use L-300C or ERG-120 Installation Tool



Extra Heavy-Duty — Series 175




CAT. NO.	LENGTH (IN.)	MAX. BUNDLE DIA.	COLOR	STD. QTY.
L-24-175-9-L	24.0	7.2"	Natural	50
L-24-175-0-L	24.0	7.2"	Black	50
L-34-175-9-L	34.0	10"	Natural	50
L-36-175-9-L	36.0	10 3/8"	Natural	50
L-36-175-0-L	36.0	10 3/8"	Black	50
L-41-175-9-L	41.0	12"	Natural	50
L-41-175-0-L	41.0	12"	Black	50
L-48-175-9-L	48.0	15"	Natural	50
L-48-175-0-L	48.0	15"	Black	50

Use L-300C Installation Tool



Sample Catalog Order:



4" Length, 18-lb. Tensile Strength, Natural Color, 100-Pack Quantity

Color Table

- | | | |
|--------------------------|-------------|-------------------------|
| 0 – Black (UV Resistant) | 5 – Green | 11 – Fluorescent Pink |
| 1 – Brown | 6 – Blue | 16 – Fluorescent Orange |
| 2 – Red | 7 – Purple | 17 – Fluorescent Yellow |
| 3 – Orange | 8 – Gray | 18 – Fluorescent Green |
| 4 – Yellow | 9 – Natural | 20 – Fluorescent Blue |

Thomas & Betts

www.tnb.com

United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Technical Services
Tel: 888.862.3289