



Pipe Straps, Pipe Clamps & Hangers (Series 700)

T&B Catalog Number:

703 1 1/2

UPC Number:

61601314370

Status:

Active

Description:

1-1/2 in. Steel Universal Clamp with GoldGalv finish. For use with Rigid/IMC, EMT conduit and Pipe.

Features

Bolt head is combination slot and hex head for flexibility of attachment

Square nut is captivated on the shoulder for easy one-handed tightening.

Straps are interchangeable with 1-1/2 in. strut, for broader application.

Straps are shipped assembled so counting and sorting are easier.

Pipe and conduit sizes are shown on the strap for easy identification.

Application

Superstrut Pipe Straps are designed to be twist inserted anywhere along the slot side of the channel.

General

Material	Steel
Finish	GoldGalv
Design Load (lbs)	800
Safety Factor	3

Dimension Information

Pipe O.D. (inches)	1.738 - 1.900
Material Thickness (ga.)	14

Packaging

T&B Order Multiple	50
Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	28.2 lbs. per 100

Application Support

Metal Framing Channels-Series 1000	Available on Website
Finishes	Available on Website
Pipes-Clamps & Hangers-Series 700	Available on Website

Certifications

RoHS Compliance	No
-----------------	----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com