



Dependable Power for Any Application

# Product Datasheet

## 600 Primary Volts - 120/240 Secondary Volts - Three Windings - 1Ø Dry Type Distribution Transformer - Single Phase

Catalog #: T253109S



### PRODUCT FEATURES

- UL listed, CSA certified
- Fully encapsulated core and coil
- Meet CSA C802.2 Efficiency
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

---

### BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

---

### UL STANDARD

UL 506

---

### CSA STANDARD

C22.2 No. 47

---

### WARRANTY

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

## GENERAL PRODUCT INFORMATION

kVA:	0.75
Primary Voltage:	600
Secondary Voltage:	120/240
Frequency:	50/60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	155°C

## PRODUCT MEASUREMENTS

Height (In./cm):	9.68 (24.6)
Width (In./cm):	4.75 (12.1)
Depth (In./cm):	4.50 (11.4)

## CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall
Knockouts (In./Cm):	0.50-0.75 (1.3-1.9)
Wiring Diagram:	9

## PACKAGING

Ship Weight (Lbs/Kg):	19 (8.6)
-----------------------	----------

## COMPLIANCES

UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No. 47
CSA Listed:	LR7357-32
Warranty:	Acme Electric Warranty Card
	<a href="http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf">www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf</a>