



Hardware & Rough-In T&B Catalog Number:

UPC Number:
Status:
Description:

12-110TB
78378612110
Active

Non-metallic Nylon Clamp, 5/8 Inch

Features

Screw hole size .203 for #10 screw
Cost effective

General

Temperature Range -40 degree F - 176 degree F

Dimension Information

Dimension D (inches)	5/8
Dimension E (inches)	21/32
Dimension T (inches)	1/16
Dimension W (inches)	1/2

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	1000
T&B Sold in UOM	Each
T&B Weight Per UOM	3.13 lbs. per 1000

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com