



Actual

**Catalog Number:** 1H3  
**Product ID:** 7TAH006100R0003  
**UPC Number:** 78378620013  
**Status:** Active

Type H High Strength Split-Bolt Connector, Bronze Alloy for Use on Copper Conductors, Conductor Range for Equal Main and Tap 2 Str-6 Sol

- Bolt and nut of high-strength corrosion-resistant bronze alloy. Copper pressure bar. Bolt and nut of hex design.
- Splicing, tapping or terminating conductors in power and grounding electrical connection.

### North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Split-Bolt
Special Features	Bolt and nut of high-strength corrosion-resistant bronze alloy. Copper pressure bar. Bolt and nut of hex design.
Application	Splicing, tapping or terminating conductors in power and grounding electrical connection.
Standard	UL E9809
Material	Bronze Alloy
Color	Metallic

### European Specifications (ETIM)

ETIM	EC000491 Earth terminal clamp
Suitable for	Round conductor
Material	Copper

### Packaging

Inner Quantity	100
Inner Dimensions (inches)	6.75x5.3x4.7
Outer Quantity	400
Outer Dimensions (inches)	11.2x10.3x7.5
Weight Uom	13 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)