

Catalog Number: 376LR-L-5240
Product ID: 7TAA121300R0050
UPC Number: 78378665534
Status: Active

200 Amp, 35kV, Loadbreak Elbow Connector with Test Point, Cable Insulation Diameter 1.180 inch to 1.465 inch. Bi-Metal Compression Lug, Conductor Size AWG Compressed Stranded 1/0 /Solid 2/0 /mmSquared 53.49.

North American Specifications (UNSPSC)

UNSPSC	39121421 Electrical connector assembly
IGCC	4586 Electrical connector assembly
Brand Name	Elastimold
Type	Loadbreak Elbow Connector with Test Point
Standard	ANSI/IEEE Standard 386.
Size	Cable Insulation Diameter 1.180 inch to 1.465 inch.
Conductor Range	Conductor Size AWG Compressed Stranded 1/0 / Solid 2/0 /mmSquared 53.49.
Material	Housing - EPDM Rubber
Color	Black
Voltage Rating	35kV
Amperage Rating	200 Amps
Insulation	Yes
Temperature Rating	-40 Degrees to +65 Degrees C
Environmental Conditions	Fully Submersible

Packaging

Outer Quantity	10
Weight Uom	3.1 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com