



Actual

**Catalog Number:** AMT250  
**Product ID:** 7TAH006400R0001  
**UPC Number:** 78378625922  
**EAN Number:** 05415022245042  
**Status:** Active

AMT Aluminum Multi-Tap Same Side Connector, 2-Port, PVC Insulated, Wire Range 250 kcmil-10 Str, Length 2.12 Inches, Width 2.13 Inches, Height 2.13 Inches, Hex Size 5/16 Inch

- PVC Insulation eliminates insulation failures and reduces outage costs. Removable port and screw plugs.
- Compact design provides space efficiencies.
- All cable entry are equipped with an anti-oxidation compound.

### North American Specifications (UNSPSC)

UNSPSC	39121410 Terminal blocks
IGCC	4547 Terminal blocks
Brand Name	Blackburn
Type	AMT Connectors
Special Features	PVC Insulation eliminates insulation failures and reduces outage costs. Removable port and screw plugs.
Standard	UL E9809
Wire Size	250kcmil-10 Str
Material	Aluminum
Color	Black

### Packaging

Outer Quantity	25
Outer Dimensions (inches)	7.9x6.7x7.7
Weight Uom	24.5 lbs. per 100

### Documents / Support Tools

SDS US 1	sds-00041-tb2
Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)