



Actual

Catalog Number: S225BB
Product ID: 7TAH006830R0004
UPC Number: 78378613036
Status: Active

Type S - Copper End-to-End Splice Connector for Conductor Range 1 Str.-4/0 Str.

- Cast of high strength copper alloy.
- Plated steel socket head set screws.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Copper Connectors
Special Features	Cast of high strength copper alloy.
Standard	UL E9809
Material	Copper
Conductor Range (Main/Primary)	1 Str-4/0 Str

Packaging

Inner Quantity	25
Outer Quantity	250
Outer Dimensions (inches)	7.3x3.8x5.3
Weight Uom	24.81 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com