



Carlon®

Outlet Boxes
T&B Catalog Number:

BH353A
 03448114585
 Active

UPC Number:
Status:
Description:

3-gang 53 cu.in. SuperBlue hard shell non-metallic outlet box with nails.
Header

Type_IDW Outlet Box

Features

- Largest wire fill capacity in their class.
- Will not crack or break in extreme environments.
- Resists flexing, hold their shape.
- Molded-in flanges and clamps
- Faster installation.
- Noncorrosive and nonconductive

Application

- Listed for masonry walls
- All PVC boxes are permissible for use with 90 degree C connectors.

General

Material	Non-Metallic
Color	Blue
Wiring System	Non-metallic sheathed cable
Volume (cu.in.)	53
Work	New
Mounting Method	Nails
Number of Gangs	Three

Dimension Information

Length (inches)	5 7/8
Width (inches)	3 3/4
Depth (inches)	3 1/2

Packaging

T&B Order Multiple	24
Package in Units	24
T&B Sold in UOM	Each
T&B Weight Per UOM	0.58 lbs. Each

Application Support

T&B Sales Drawings	wsd-ac03644
Product Overview-Carlon SuperBlue PVC Available on Website Boxes	

Certifications



File Nbr:
 E 42728

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com