

Carlon®

Rigid Non-Metallic Conduit Bodies & Covers

T&B Catalog Number:

E985F-CAR

UPC Number:


03448113244

Status:

Active

Description:

1 inch Rigid non-metallic Type LR conduit body.



Features

Textured lids

Foam-in-place gasket

Application

For use with rigid/IMC conduit

General

Trade Size (inches)

1

Material

Non-Metallic

Volume (cu.in.)

12

Conduit Body Shape

LR

Dimension Information

C (inches)

29/32

H (inches)

1 25/32

L1 (inches)

6 9/32

L2 (inches)

5 9/32

L3 (inches)

4 25/32

Q (inches)

1 3/4

W (inches)

2 1/32

Packaging

T&B Order Multiple

10

Package in Units

10

T&B Sold in UOM

Each

T&B Weight Per UOM

0.42 lbs. Each

Application Support

T&B Sales Drawings

wsd-ac04179

Rigid Non-metallic Conduit Bodies

Available on Website

Specifications & Applications

Available on Website

Certifications



File Nbr:

E 42728

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com