


# Catamount®

## Cable Ties



### INTERMEDIATE - SERIES 30

Per Bag	Item Number	Material	Color	Bundle Diameter		Length		Width		Minimum Loop Tensile LB (kg)
				Inch	(mm)	Inch	(mm)	Inch	(mm)	
100	L-5-30HS-0-C	Heat Stabilized Nylon	Black	1/16 - 1/4	(2 - 32)	5.6	(145)	.130	(3)	30 (13.6)
1000	L-5-30HS-0-M									
100	L-5-30-0-C	UV Nylon								
1000	L-5-30-0-M									
100	L-5-30-9-C	Nylon	Natural							
1000	L-5-30-9-M									
100	P-5-30-1-C	Nylon Colors	Brown							
	P-5-30-2-C		Red							
	P-5-30-3-C		Orange							
	P-5-30-4-C		Yellow							
	P-5-30-5-C		Green							
	P-5-30-6-C		Blue							
	P-5-30-8-C		Gray							
	L-8-40HS-0-C		Heat Stabilized Nylon	Black	1/16 - 2	(2 - 51)	8.5	(215)	.146	(4)
1000	L-8-40HS-0-M									
100	L-8-40-0-C	UV Nylon								
1000	L-8-40-0-M									
100	L-8-40-9-C	Nylon	Natural							
1000	L-8-40-9-M									
100	P-8-40-1-C	Nylon Colors	Brown							
	P-8-40-2-C		Red							
	P-8-40-3-C		Orange							
	P-8-40-4-C		Yellow							
	P-8-40-5-C		Green							
	P-8-40-6-C		Blue							
	P-8-40-7-C		Purple							
	P-8-40-8-C		Gray							
500	L-11-40-0-C	UV Nylon	Black							
100	L-11-40-9-C	Nylon	Natural	1/16 - 3	(2 - 76)	11.5	(282)			
500	L-11-40-9-D									
100	L-14-40-0-C	UV Nylon	Black	1/16 - 4	(2 - 102)	14.5	(358)			
500	L-14-40-0-D									
100	L-14-40-9-C	Nylon	Natural							
500	L-14-40-9-D									

• Use QC-100, L-200, L-400, L-400C, or ERG-299 Installation Tools