



Conduit Fittings-PVC Coated

T&B Catalog Number:

CPL3/4-G

UPC Number:

70450836255

Status:

Active

Description:

3/4 in. Dark Gray 40 mil PVC Coated Galvanized Rigid Steel Coupling.

Features

Nominal .002 in. (2 mil) blue urethane coating on interior and exterior

Minimum .040 in. (40 mil) PVC coating is bonded to the exterior

Straight threads (NPS)

Molded ribs on outer coating for easy installation, up to and including 4 in.

Pressure sealing sleeves protect your connection

General

Trade Size (inches)	3/4
Material	Steel
Finish	PVC Coated
Color	Dark Gray

Dimension Information

Pipe Size (inches)	3/4
Pipe Size (Metric Size Designator*)	21

Technical Information

Chemical Resistance Chart	Available on Website
---------------------------	----------------------

Specifications

Ocal Specification Guide-1995 Master Format-PDF	Available on Website
Ocal Specification Guide-1995 Master Format-DOC	Available on Website
Ocal Specification Guide-2004 Master Format-PDF	Available on Website
Ocal Specification Guide-2004 Master Format-DOC	Available on Website

Packaging

Package in Units	90
T&B Sold in UOM	Each
T&B Weight Per UOM	0.28 lbs. Each

Application Support

T&B Sales Drawings	wsd-000545
Ocal PVC Coated Conduit System	Available on Website
Ocal Specifications	Available on Website
Recommended Installation Procedures	Available on Website
Product Overview-Conduit Outlet Bodies	Available on Website
NEMA Standards-RN 1	Available on Website
NEC 310-16 - Conductors for General Wiring	Available on Website
NEC Table 8	Available on Website

Notes

Metric size designator (ANSI C80. 1-1994)

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E 46453

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com