



Actual

**Catalog Number:** **BG810A**  
**Product ID:** 7TAA010220R0017  
**UPC Number:** 78599190699  
**Status:** Active

Bushing, Insulated Grounding, Trade Size 4 Inches, Grounding Lug Wire Size 14 AWG - 2/0 AWG, Malleable Iron, For use with Rigid/IMC Conduit.

### North American Specifications (UNSPSC)

UNSPSC	39121312 Electrical bushing
IGCC	4442 Electrical bushing
Brand Name	Steel City
Type	Grounding Bushings
Special Features	105 degree C thermoplastic liners, heavy reinforced ribs.
Application	For use with rigid/IMC conduits
Standard	UL e3060
Size	4
Material	Zinc Die Cast
Finish	Zinc Plated

### European Specifications (ETIM)

ETIM	EC002357 Support insulator
Length	146.8374mm
Outer diameter	127mm

### Packaging

Outer Quantity	10
Outer Dimensions (inches)	10.2x8.4x7.9
Weight Uom	46.5 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)