



Representative

**Catalog Number:** 123AL  
**Product ID:** 7TAD013490R0012  
**UPC Number:** 78621080107  
**Status:** Active  
**Replacement Catalog:** 1223AL

3/4 Inch Aluminum Bushing for Use with Rigid/IMC Conduit

- High ribs make tightening easy with fingers or with wrench.
- Locknut-type base gives improved bonding and resist loosening under conditions of vibration.

#### Header

3D Model Available on Website

#### North American Specifications (UNSPSC)

UNSPSC	39121312 Electrical bushing
IGCC	4442 Electrical bushing
Brand Name	T&B
Type	Conduit Bushing
Special Features	Smoothly Rounded Shoulder Covers End of Conduit; Broad Flange Covers Knockout Hole.
Application	For Use with Rigid/IMC Conduit
Standard	UL E23018
Size	3/4 Inch
Material	Aluminum

#### European Specifications (ETIM)

ETIM	EC001181 Sealing ring
Model	Other
Outer diameter	31.75mm
Material	Metal
Fitting for thread size NPT	0.75

#### Packaging

Inner Quantity	100
Inner Dimensions (inches)	6x4.5x3
Outer Quantity	1000
Outer Dimensions (inches)	6.2x4.8x4.1
Weight Uom	9.38 lbs. per 1000

#### Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000019

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)