



Representative

Catalog Number: 126
Product ID: 7TAD013490R0017
UPC Number: 78621000126
EAN Number: 05414363137160
Status: Active
Replacement Catalog: 1226

1-1/2 Inch Steel Bushing for Use with Rigid/IMC Conduit

- High ribs make tightening easy with fingers or with wrench.
- Locknut-type base gives improved bonding and resist loosening under conditions of vibration.

Header

3D Model	Available on Website
----------	----------------------

UNSPSC Specifications

UNSPSC	39121312 Electrical bushing
IGCC	4442 Electrical bushing
Brand Name	T&B
Type	Bushings
Special Features	Smoothly rounded shoulder covers end of conduit; broad flange covers knockout hole.
Application	For Use with Rigid/IMC Conduit
Standard	UL E23018, CSA
Size	1-1/2 Inch
Material	Steel

Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x4x4
Outer Quantity	100
Outer Dimensions (inches)	11x8.6x6.1
Weight Uom	11.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000019

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com