



## Armored Cable/Flexible Metal Conduit Fittings

**T&B Catalog Number:**

2492

**UPC Number:**

78621002492

**Status:**

Active

**Description:**

Metal-Clad and Armored Cable Fitting, Straight, Trade Size 3/8 Inch, Knockout Size 1/2 Inch, Cable Range 0.370 to 0.500 Inch, Steel with Zinc Plating, Nylon Insulated

### Features

Unique saddle design firmly secures cable in place, provides holding power in excess of listing agency requirements and assures high quality bonding.

Removable bushing design covers wide range, reduces inventories.

One screw provides quick installation

### Application

For use with Armored Cable and Flexible Metal Conduit.

To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

Can be used on smooth or corrugated aluminum sheathed and steel metal clad cable.

### General

Trade Size (inches)

3/8

Material

Steel

Finish

Electro Zinc Plated

### Dimension Information

Dimension A (inches)

1 3/16

Dimension B (inches)

1 3/8

Dimension C (inches)

7/16

Knockout Size (inches)

1/2

### Specifications

3dmodel

Available on Website

### Packaging

T&B Inner Pack

100

Package in Units

500

T&B Sold in UOM

Each

T&B Weight Per UOM

7.12 lbs. per 100

### Notes

U.L. Listed as a grounding means for steel MC cable and ALS. For dry locations.

Tite-Bite® Connectors are approved for continuous sheathed corrugated MC cable.

### Certifications

RoHS Compliance

No

## Certifications



File Nbr:  
E 38947

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)