



Liquidtight Flexible Cord & Cable Fittings

T&B Catalog Number:

2634

UPC Number:

78621002634

Status:

Active

Description:

Chase Liquidtight Steel Cord Connector, Straight, 1/2 Inch, Cord Range 0.450 to 0.560 Inch

Application

Suitable for use in hazardous locations in Class I, Div. 2; Class II, Div 1 & 2; Class III, Div 1 & 2, where general purpose equipment is specifically permitted by NEC 500-2(a).

Meets Coast Guard CG293

General

Material Steel

Dimension Information

Hub Size (inches) 1/2
 Dimension A (inches) 1 1/16
 Dimension B (inches) 1 3/16
 Cord Range (inches) .450-.560

Specifications

3dmodel Available on Website
 Temperature Rating 105 C

Packaging

T&B Inner Pack 25
 Package in Units 50
 T&B Sold in UOM Each
 T&B Weight Per UOM 19.5 lbs. per 100

Application Support

Product Overview Available on Website
 Portable Cord Selection Table Available on Website

Notes

Suitable for use in hazardous locations in Class I, Div. 2; Class II, Div 1 & 2; Class III, Div 1 & 2, where general purpose equipment is specifically permitted by NEC 500-2(a).

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125

T&B Technical Support
MS 3B-50
8155 T&B Blvd.

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289

