



Armored Cable/Flexible Metal Conduit Fittings

T&B Catalog Number:

267

UPC Number:

78621000267

Status:

Active

Description:

Squeeze Connector, 45 Degree Bend, Trade Size 1/2 Inch, Knockout Size 1/2 Inch, Cable Range 0.813 to 0.937 Inch, Steel

Features

Fast and easy installation, simply loosen screws partway to lift off cap.

Application

For use with Armored Cable and Flexible Metal Conduit.

General

Trade Size (inches)	1/2
Material	Steel
Finish	Zinc Plate

Dimension Information

Dimension A (inches)	1 23/32
Dimension B (inches)	1/2
Dimension C (inches)	1 1/4
Knockout Size (inches)	1/2
Cable Opening-Minimum (inches)	0.813
Cable Opening-Maximum (inches)	0.937

Packaging

T&B Inner Pack	25
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	17.31 lbs. per 100

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com

